


# Technical Data



## ACRYLIC PAINTS

### RAL COLOUR MATCHED ACRYLIC PAINTS

9011	Matt Black
9010	Matt White
9005	Gloss Black
9016	Gloss White
3002	Bright Red
5015	Blue
7032	Battleship Grey
6002	Green
1018	Bright Yellow
	Fluorescent Green
	Fluorescent Yellow
	Fluorescent Red
	Cerise
7035	Rittal Grey
5010	Ford Blue
1007	JCB Yellow
3000	Massey Ferguson Red
6001	John Deere Green
2004	Belle Orange

#### GENERAL DESCRIPTION

Ambersil Acrylic Paint is an acrylic based coating, delivered in an aerosol can, available in a wide variety of RAL colours.

#### FEATURES

- Fast drying
- Good hardening
- Excellent flexibility
- High UV resistance
- Good adhesion to metal, wood, glass, paintable plastics, concrete, & stone
- Does not contain any heavy metals
- Good opacity – masks surface imperfections
- Long lasting, high gloss finish

#### APPLICATIONS

Ambersil Acrylic Paint is recommended as a protective coating for the repair of lacquered surfaces. Ambersil Acrylic Paint may also be used as a high quality paint for a wide variety of applications in the following areas:

- Industry
- Automotive
- Home and garden

#### DIRECTIONS

- Shake aerosol can well for at least two minutes after agitator ball is free. Repeat frequently during use
- Apply to a clean, degreased, dry surface for best results. Remove rust and scale with a wire brush. Use an anti-corrosion primer such as Ambersil Zinc Primer or Ambersil Cold Galvanise to provide maximum corrosion resistance and durability
- Use the can in an upright position
- Apply in light, even coats - best results are obtained with 2 – 3 lighter rather than 1 heavy coat. Additional coats can be applied after 3 - 5 minutes and within 30 minutes
- When spraying is finished, clear aerosol valve by turning can upside down and press button until only propellant escapes.
- Do not use on energised equipment. Use in well ventilated area

NB Colours are representative only, please test suitability prior to use

## TECHNICAL DATA

Resin Type	:	Acrylic
Colour	:	Standard RAL shades
Gloss (60° angle)		
Matt	:	15 ± 5 E
Gloss	:	85 ± 5 E
Particle Size	:	< 10 µ
Drying Time (20°C ; 50%RH)		
Dust Free	:	< 10 min
To Touch	:	< 20 min
To Handle	:	< 60 min
Over-coatable	:	after 5 min
Adhesion (Gt)	:	0 - 1
Packaging	:	400ml

## STORAGE

The product may be stored at normal ambient temperatures and has a shelf life of not less than 120 months with correct storage. Aerosols should always be stored below 50°C, away from direct heat and naked flame.

## HEALTH AND SAFETY

Health and Safety sheet available separately.

## TECHNICAL SERVICE

CRC Industries UK Ltd provides a technical support service and maintains a constant programme of research and development. We are able to assist customers by specific product development to meet particular requirements.

## MISREPRESENTATION ACT 1967

## TRADE DESCRIPTIONS ACT 1968

The information given in this publication is based on our experience and reports from customers. There are many factors outside our control and knowledge which affect the use and performance of our products and for which reason no warranty is given, express or implied. Users should make their own tests to determine the applicability of such information or the suitability of any products for their own particular purposes. Statements concerning the use of the products described herein are not to be construed as recommending the infringement of any patent and no liability for infringement arising out of any such use is to be assumed.

CRC Industries UK Limited, Wylds Road, Bridgwater, Somerset, TA6 4DD

Tel: +44 (0) 1278 727200

Fax: +44 (0) 1278 425644

Web: [www.ambersil.com](http://www.ambersil.com)

E-mail: [sales.uk@crcind.com](mailto:sales.uk@crcind.com)