

Dial Thickness Gages

SERIES 7



7301



7321

The Dial Thickness Gages offer a quick and efficient means of inspection with their convenient grip handle, thumb trigger and spring-loaded spindle. The various models cover a wide range of applications.

SPECIFICATIONS

Metric

Graduation	Range	Order No.	Mass	Remarks (Applications)
0.001mm	0 - 1mm	7327	230g	Type A: Standard type
0.01mm	0 - 10mm	7301	212g	Type A: Standard type
		7321	371g	Type B: Deep throat type
		7313	224g	Type C: For lens thickness
		7315	217g	Type D: For groove thickness
		7360	199g	Type E: For tube thickness
	0 - 20mm	7305	217g	Type A: Standard type
		7323	371g	Type B: Deep throat type


Inch

Graduation	Range	Order No.	Mass	Remarks (Applications)
.0001 "	0 - .05 "	7326	.5 lbs.	For paper (film, wire) thickness
.001 "	0 - .4 "	7300	.47 lbs.	Type A: Standard type
		7320	.82 lbs.	Type B: Deep throat type
	0 - 1 "	7304	.48 lbs.	Type A: Standard type


Dimensions

Standard (Type A)


Unit: mm




Deep throat (Type B)



Lens thickness (Type C)



Groove (Type D)



Tube thickness (Type E)

