

AC FILTERING

FLA* RoHS Compliant



The FLA series uses metallized polypropylene dielectric, aluminum can, impregnated with soft PU specially treated to have a very high dielectric strength in operating conditions up to 85°C.

The FLA has been designed with overpressure disconnected device. They are suitable for output AC filtering for power converters, UPS systems, solar inverters and motor drives etc.

APPLICATIONS

- The FLA capacitor is particularly designed for AC filtering.

HOT SPOT CALCULATION

See Hot Spot Temperature, page 70.

$$\theta_{\text{hot spot}} = \theta_{\text{ambient}} + (P_d + P_t) \times R_{th}$$

with P_d (Dielectric losses) = $Q \times \text{tg}\delta_0$

$$Q \times \text{tg}\delta_0 \Rightarrow \left[\frac{1}{2} \times C_n \times (V_{\text{peak to peak}})^2 \times f \right] \times \text{tg}\delta_0$$

$\text{tg}\delta_0$ (tan delta)

For polypropylene, $\text{tg}\delta_0 = 2 \times 10^{-4}$ for frequencies up to 1MHz and is independent of temperatures.

$$P_t \text{ (Thermal losses)} = R_s \times (I_{rms})^2$$

where C_n in Farad I_{rms} in Ampere f in Hertz
 V in Volt R_s in Ohm θ in °C
 R_{th} in °C/W

WORKING TEMPERATURE

According to the power to be dissipated
 -40°C to +85°C

LIFETIME EXPECTANCY

One unique feature of this technology (as opposed to aluminum electrolytics) is how the capacitor reacts at the end of its lifetime.

Unlike aluminum electrolytic film capacitors do not have a catastrophic failure mode. Film capacitors simply experience a parametric loss of capacitance of about 5% from initial value, with no risk of short circuit.

The capacitor continues to be functional even after this 5% decrease.

PACKAGING MATERIAL

- Aluminium can with soft PU

STANDARDS

IEC 61071-1, IEC 61071-2: Power electronic capacitors
 EN CYWT2.E514025 Certificate: E514025 (approved by UL)

HOW TO ORDER

FLA



Series

B2



Case

A1-A2
 B1-B4
 C1
 D1
 E1-E8
 F1-F5
 G1-G6
 H1-H2

6



Dielectric

6 = Polypropylene

A



Voltage

A = 250Vrms
 H = 330Vrms
 L = 450Vrms
 M = 480Vrms
 J = 550Vrms
 R = 600Vrms
 N = 660Vrms
 O = 690Vrms
 P = 850Vrms

0606



Capacitance

EIA Code
 0606 = 60uF

K



Tolerances

J = ±5%
 K = ±10%

F




Terminal Code



F = Fast-on terminals
 H = M8 screw terminals




LIFETIME EXPECTANCY VS HOT SPOT TEMPERATURE AND VOLTAGE



GENERAL DESCRIPTION



Fast-on terminals



M 8 screw terminals

DIMENSIONS

Case Ref	OD (mm)	H (mm)
A1	45	100
A2	45	125
B1	50	75
B2	50	100
B3	50	125
B4	50	150
C1	55	125
D1	60	130
E1	63.5	70
E2	63.5	75
E3	63.5	80
E4	63.5	100
E5	63.5	125
E6	63.5	150
E7	63.5	165
E8	63.5	197
F1	75	107
F2	75	122
F3	75	152
F4	75	180
F5	75	197
G1	85	122
G2	85	152
G3	85	180
G4	85	197
G5	85	210
G6	85	247
H1	106	210
H2	106	247

INSTALLATION TORQUE

Terminals	Torque Nm
Terminals	Torque Nm
M8	6
Stud of Case	Torque Nm
M10	10
M12	15

