

Ordering information :

2557 P *** 000

1 2 3 4

RoHS COMPLIANT

1. Series No.

2. No. of circuits

3. Plating :

T= Tin plated 120μ " min over 30μ " min. nickel overall

U= Gold flash over 30μ " min. nickel overall

J= 15μ " min. Selective gold on contact area over 30μ " min. nickel overall,

Tin plated on solder or other area



4. Special options

*** 2557 Series ***



Material :

* Insulator : PBT UL94V-0


* Contact : Brass



Recommended hole pattern



CIRCUITS	PART NO.	DIMENSION		CIRCUITS	PART NO.	DIMENSION	
		A	B			A	B
2	2557P02*000	2.540(.100)	5.1(.200)	21	2557P21*000	50.800(2.000)	53.3(2.098)
3	2557P03*000	5.080(.200)	7.6(.299)	22	2557P22*000	53.340(2.100)	55.9(2.201)
4	2557P04*000	7.620(.300)	10.2(.402)	23	2557P23*000	55.880(2.200)	58.4(2.299)
5	2557P05*000	10.160(.400)	12.7(.500)	24	2557P24*000	58.420(2.300)	61.0(2.402)
6	2557P06*000	12.700(.500)	15.2(.298)	25	2557P25*000	60.960(2.400)	63.5(2.500)
7	2557P07*000	15.240(.600)	17.8(.701)	26	2557P26*000	63.500(2.500)	66.0(2.598)
8	2557P08*000	17.780(.700)	20.3(.799)	27	2557P27*000	66.040(2.600)	68.6(2.701)
9	2557P09*000	20.320(.800)	22.9(.902)	28	2557P28*000	68.580(2.700)	71.1(2.799)
10	2557P10*000	22.860(.900)	25.4(1.000)	29	2557P29*000	71.120(2.800)	73.4(2.890)
11	2557P11*000	25.400(1.000)	27.9(1.098)	30	2557P30*000	73.660(2.900)	76.2(3.000)
12	2557P12*000	27.940(1.100)	30.5(1.201)	31	2557P31*000	76.200(3.000)	78.7(3.098)
13	2557P13*000	30.480(1.200)	33.0(1.299)	32	2557P32*000	78.740(3.100)	81.3(3.201)
14	2557P14*000	33.020(1.300)	35.6(1.402)	33	2557P33*000	81.280(3.200)	83.8(3.299)
15	2557P15*000	35.560(1.400)	38.1(1.500)	34	2557P34*000	83.820(3.300)	86.4(3.402)
16	2557P16*000	38.100(1.500)	40.6(1.598)	35	2557P35*000	86.360(3.400)	88.9(3.500)
17	2557P17*000	40.640(1.600)	43.2(1.701)	36	2557P36*000	88.900(3.500)	91.4(3.598)
18	2557P18*000	43.180(1.700)	45.7(1.799)	37	2557P37*000	91.440(3.600)	94.0(3.701)
19	2557P19*000	45.720(1.800)	48.3(1.902)	38	2557P38*000	93.980(3.700)	96.5(3.799)
20	2557P20*000	48.260(1.900)	50.8(2.000)	39	2557P39*000	96.520(3.800)	99.1(3.902)
				40	2557P40*000	99.060(3.900)	101.6(4.000)

G	ES101242			LEOCO CORPORATION GENERAL TOLERANCES: (UNLESS SPECIFIED) <table><thead><tr><th></th><th>mm</th><th>inch</th></tr></thead><tbody><tr><td>1 PLACE</td><td>± 0.30</td><td>± —</td></tr><tr><td>2 PLACES</td><td>± 0.20</td><td>± .012</td></tr><tr><td>3 PLACES</td><td>± 0.10</td><td>± .008</td></tr><tr><td>4 PLACES</td><td>± —</td><td>± .004</td></tr></tbody></table> ANGULAR ± (1°)		mm	inch	1 PLACE	± 0.30	± —	2 PLACES	± 0.20	± .012	3 PLACES	± 0.10	± .008	4 PLACES	± —	± .004	APPROVED:		PART NO.:			
	mm	inch																							
1 PLACE	± 0.30	± —																							
2 PLACES	± 0.20	± .012																							
3 PLACES	± 0.10	± .008																							
4 PLACES	± —	± .004																							
F	ES071009				DATE:		2557P***000																		
E	ES060535				CHECKED:		TITLE:																		
					DATE:		HEADER																		
D	E970242				DRAWN:		DRAWING NO.:																		
				DATE:		255701S																			
A	DWG REL					UNITS	SCALE	SIZE	SHEET	REV.															
REV.	ECO. NO.	CHG.	APP.			$\frac{\text{mm}}{\text{inch}}$	2:1	A4	1/1	G															