



131S/133S Series

Numeric Display/Case Size 7.0 x 11.0 mm

Features

Case Size	7.0 x 11.0 mm (W x H)						
Product features	• Each color has anode common and cathode common respectively. • A black case and a gray case are available. • Lead-free soldering compatible • RoHS compliant						
Peak wavelength	<table><tr><td>Green</td><td>: 565nm</td></tr><tr><td>Orange</td><td>: 605nm</td></tr><tr><td>Red</td><td>: 660nm</td></tr></table>	Green	: 565nm	Orange	: 605nm	Red	: 660nm
Green	: 565nm						
Orange	: 605nm						
Red	: 660nm						
Number of Digit	1 Digit						
Segment Shape	Arrow Feather Type						
Character Height	8.0 mm						
Die materials	<table><tr><td>Green</td><td>: GaP</td></tr><tr><td>Orange</td><td>: GaAsP</td></tr><tr><td>Red</td><td>: GaAlAs</td></tr></table>	Green	: GaP	Orange	: GaAsP	Red	: GaAlAs
Green	: GaP						
Orange	: GaAsP						
Red	: GaAlAs						
Soldering methods	TTW (Through The Wave) soldering and manual soldering						
ESD	More than 2kV(HBM)						
Packing	Tray						

Recommended Applications

Amusement Equipment, Electric Household Appliances, Other General Applications

Emitted Color

Part No.				Material	Emitted Color	Chip/ Segment
Anode Common		Cathode Common				
Case Color Black	Case Color Gray	Case Color Black	Case Color Gray			
NAG131SP-B	NAG133SP-B	NKG131SP-B	NKG133SP-B	GaP	Green	1
NAA131S-B	NAA133S-B	NKA131S-B	NKA133S-B	GaAsP	Orange	1
NAR131S-B	NAR133S-B	NKR131S-B	NKR133S-B	GaAlAs	Red	1
NAR131S-C	-	NKR131S-C	NKR133S-C	GaAlAs	Red	1

Absolute Maximum Ratings

(Ta=25°C)

Item	Symbol	Absolute Maximum Ratings			Unit
		Green	Orange	Red	
Power Dissipation	Pd	48	48	40	mW/seg
Forward Current	I _F	20	20	20	mA/seg
Pulse Forward Current ※1	I _{FRM}	80	80	80	mA/seg
Derating (Ta=25°C or higher)	ΔI _F	0.33	0.33	0.33	mA/°C
	ΔI _{FRM}	1.33	1.33	1.33	mA/°C
Reverse Voltage	V _R	4	4	4	V
Operating Temperature	T _{opr}	-30~+85	-30~+85	-30~+85	°C
Storage Temperature	T _{stg}	-30~+85	-30~+85	-30~+85	°C

※1 I_{FRM} Measurement condition : Duty 1/5, f = 1kHz


Electro-Optical Characteristics

(Ta=25°C)


Item	Conditions	Symbol		Characteristics			Unit
				Green	Orange	Red	
Luminous Intensity (-B Product)	I _F =10mA	I _V	MIN.	1	0.6	1.4	mcd/seg
			TYP.	2	1.2	2.8	
Luminous Intensity (-C Product)	I _F =10mA	I _V	MIN.	-	-	2.8	mcd/seg
			TYP.	-	-	5.6	
Forward Voltage	I _F =10mA	V _F	TYP.	2.0	2.0	1.7	V/seg
			MAX.	2.4	2.4	2.0	
Reverse Current	V _R =4V	I _R	MAX.	100	100	100	μA/seg
Peak Wavelength	I _F =10mA	λ _p	TYP.	565	605	660	nm
Spectral Line Half Width	I _F =10mA	Δλ	TYP.	30	30	30	nm

Technical Data(Green)


Forward Voltage vs. Forward Current
Condition : $T_a = 25^\circ\text{C}$




Ambient Temperature vs. Forward Voltage



Forward Current vs. Relative Intensity
Condition : $T_a = 25^\circ\text{C}$




Ambient Temperature vs. Relative Intensity
Condition : $I_F = 10\text{mA}$




Technical Data(Green)


Ambient Temperature vs. Maximum Forward Current



Ambient Temperature vs. Power Dissipation




Duty Factor vs. Maximum Tolerable Pulse Forward Current
Condition: $T_a = 25^\circ\text{C}$




Technical Data(Orange)


Forward Voltage vs. Forward Current
Condition : $T_a = 25^\circ\text{C}$




Ambient Temperature vs. Forward Voltage



Forward Current vs. Relative Intensity
Condition : $T_a = 25^\circ\text{C}$




Ambient Temperature vs. Relative Intensity
Condition : $I_F = 10\text{mA}$




Technical Data(Orange)


Ambient Temperature vs. Maximum Forward Current



Ambient Temperature vs. Power Dissipation




Duty Factor vs. Maximum Tolerable Pulse Forward Current
Condition : $T_a = 25^\circ\text{C}$




Technical Data(RED)


Forward Voltage vs. Forward Current
Condition : $T_a = 25^\circ\text{C}$




Ambient Temperature vs. Forward Voltage



Forward Current vs. Relative Intensity
Condition : $T_a = 25^\circ\text{C}$




Ambient Temperature vs. Relative Intensity
Condition : $I_F = 10\text{mA}$




Technical Data(RED)


Ambient Temperature vs. Maximum Forward Current



Ambient Temperature vs. Power Dissipation




Duty Factor vs. Maximum Tolerable Pulse Forward Current
Condition : $T_a = 25^\circ\text{C}$



Package Dimensions

(Unit: mm)




※1 : The length of lead base.

※2 : When the emitted color is red, the polarity of DP No.6 pin is an anode, and DP No.7 pin is a cathode.

But when the emitted color is green or orange, the polarity reverses.

Recommended Soldering Pattern

(Unit: mm)





TTW (Through The Wave) soldering Conditions

Pre-heating	100 °C 60 s	(MAX.) Resin surface temperature (MAX.)
Solder Bath Temp.	265 °C	(MAX.)
Dipping Time	5 s	(MAX.)
Position	At least 2.0 mm away from the root of lead	

- 1) The dip soldering process shall be 2 times maximum.
- 2) The product shall be cooled to normal temperature before the second dipping process.

Manual Soldering Conditions

Iron tip temp.	400 °C	(MAX.) (30 W Max.)
Soldering time and frequency	3 s 2 times	(MAX.) (MAX.)
Position	At least 2.0 mm away from the root of lead	

Reliability Testing Result

Reliability Testing Result	Applicable Standard	Testing Conditions	Duration	Failure
Room Temp. Operating Life	BAJED-4701/100(101)	Ta = 25°C, If = Maximum Rated Current/seg	1,000 h	0/10
Resistance to Soldering Heat	BAJED-4701/300(302)	260±5°C, 3mm from package base	10s	0/10
Temperature Cycling	BAJED-4701/100(105)	Minimum Rated Storage Temperature(30min) ~Normal Temperature(15min) ~Maximum Rated Storage Temperature(30min) ~Normal Temperature(15min)	5 cycles	0/10
Wet High Temp. Storage Life	BAJED-4701/100(103)	Ta = 60±2°C, RH = 90±5%	1,000 h	0/10
High Temp. Storage Life	BAJED-4701/200(201)	Ta = Maximum Rated Storage Temperature	1,000 h	0/10
Low Temp. Storage Life	BAJED-4701/200(202)	Ta = Minimum Rated Storage Temperature	1,000 h	0/10
Lead Tension	BAJED-4701/400(401)	5N, 1time	10s	0/10
Vibration, Variable Frequency	BAJED-4701/400(403)	98.1m/s ² (10G), 100 ~ 2KHz sweep for 20min., XYZ each direction	2 h	0/10
Lead Bend	BAJED-4701/400(401)	2.5N, 0° ↔ 90°	Twice	0/10
Shock	JSC 7201 A-8	It falls on wood engraving from height of 75cm.	3 times	0/10

Failure Criteria

Items	Symbols	Conditions	Failure criteria
Luminous Intensity	Iv	If = Value of each product Luminous Intensity	Testing Min. Value < Spec. Min. Value x 0.5
Forward Voltage	V _F	If = Value of each product Forward Voltage	Testing Max. Value ≥ Spec. Max. Value x 1.2
Reverse Current	I _R	V _R = Maximum Rated Reverse Voltage V	Testing Max. Value ≥ Spec. Max. Value x 2.5
Cosmetic Appearance	-	-	Occurrence of notable decoloration, deformation and cracking

Special Notice to Customers Using the Products and Technical Information Shown in This Data Sheet

- 1) The technical information shown in the data sheets are limited to the typical characteristics and circuit examples of the referenced products. It does not constitute the warranting of industrial property nor the granting of any license.
- 2) For the purpose of product improvement, the specifications, characteristics and technical data described in the data sheets are subject to change without prior notice. Therefore it is recommended that the most updated specifications be used in your design.
- 3) When using the products described in the data sheets, please adhere to the maximum ratings for operating voltage, heat dissipation characteristics, and other precautions for use. We are not responsible for any damage which may occur if these specifications are exceeded.
- 4) The products that have been described to this catalog are manufactured so that they will be used for the electrical instrument of the benchmark (OA equipment, telecommunications equipment, AV machine, home appliance and measuring instrument).
The application of aircrafts, space borne application, transportation equipment, medical equipment and nuclear power control equipment, etc. needs a high reliability and safety, and the breakdown and the wrong operation might influence the life or the human body. Please consult us beforehand if you plan to use our product for the usages of aircrafts, space borne application, transportation equipment, medical equipment and nuclear power control equipment, etc. except OA equipment, telecommunications equipment, AV machine, home appliance and measuring instrument.
- 5) In order to export the products or technologies described in this data sheet which are under the "Foreign Exchange and Foreign Trade Control Law," it is necessary to first obtain an export permit from the Japanese government.
- 6) No part of this data sheet may be reprinted or reproduced without prior written permission from Stanley Electric Co., Ltd.
- 7) The most updated edition of this data sheet can be obtained from the address below:
<http://www.stanley-components.com>