

Rubber Foot SK-Type



Characteristic

A foot for various industrial devices.

Specification


A Washer is not included in SK-95.
The shape of SK-2519 is slightly different from others.

Parts List

No.	Part Name	Material	Finish
1	Rubber Foot	EPDM(Hardness: 65 $\pm$ 5°)	Black
2	Washer	SPCC	Zn

Application

Office automation appliances /
Medical instruments /
Home appliances / Furniture / Toys, etc.



Model No.	Recommended Screw	Recommended Screw Torque mN·m (kgf·cm)	Allowable Maximum Load N (kgf)	A	B	C	D	E	F	G	Net Weight (g)	Code No.
SK-95	M2 Pan Head	10(0.1)	20 (2.0)	9	7	5	3	2	4	R 1	0.4	5259
SK-13	M2.5 Truss	39(0.4)	60 (6.1)	13	13	5	2		6	R 3	0.8	5260
SK-156	M3 Pan Head	59(0.6)	90 (9.2)	15	15	6	3	3	7	R 1	1.4	5261
SK-1910	M3 Pan Head	88(0.9)	100(10.2)	19	19	10	5			R 4.75	3.7	5262
SK-1912	M4 Pan Head	118(1.2)	140(14.3)			12	7	4	9	R 2.5	4.8	5263
SK-209	M3 Pan Head	59(0.6)	140(14.3)	20	17	9	5	3	7	R 2	3.5	5264
SK-2010	M3 Pan Head	108(1.1)	110(11.2)		16	10	4		8	R 1.5	3.3	5265
SK-259	M5 Pan Head	128(1.3)	200(20.4)	25	21	9	5	5	10	R 2	5.7	5266
SK-2519	M5 Pan Head	118(1.2)	80 (8.2)		25	14	9		11	R17	6.4	5267

TM-136 Rubber Foot



Characteristic


A single screw is all you need to install.
A foot for various industrial devices.

Note

Due to commercial product, dimension might change without notice.
The hole for installation screw might not transfix.

Application

Machine tools /
Measuring instruments /
Telecommunication devices /
Computers



Model No.	Material		Color
	Product No.1 to 6	Product No.7 and 8	
TM-136	SBR	NR	Black

Model No.	Recommended Screw	Recommended Screw Torque mN·m (kgf·cm)	Allowable Maximum Load N (kgf)	A	B	C	D	E	F	Net Weight (g)	Code No.
TM-136-1	M2.5 Countersunk	20(0.2)	35 (3.6)	13	6.5	—	2.5	5.5	2	1.0	7011
TM-136-2	M2.5 Pan Head	29(0.3)	85 (8.7)	16	7.5	12			3	1.4	7012
TM-136-4	M3 Pan Head	29(0.3)	130(13.3)	19	8	15		6	4	2.8	7014
TM-136-5	M3 Pan Head	49(0.5)	100(10.2)			14	3		6	3.3	7015
TM-136-6	M3 Pan Head	39(0.4)	150(15.3)	22	10	17		8		4.7	7016
TM-136-7	M3 Pan Head	39(0.4)	290(29.6)	27		24		13	5	6.1	7017
TM-136-8	M6 Pan Head	196(2.0)	460(46.9)	29	14	29	6	14	8	14.0	7018