




### Description:

Statfree DLR material meets the working surface requirements of EN61340-5-1. This material is a dual purpose rubber matting material. The two layer construction allows it to be used as a dissipative or a conductive matting product. The soft dissipative layer makes an excellent table mat, ideal for use in soldering and assembly areas. This rubber material has superior resistance to heat, abrasion, chemicals, and is easy to clean and maintain. Statfree DLR material will not melt and does not burn when coming into contact with hot metal parts or soldering debris. It is amine, chloride, sulfide, alumina, and magnesia free.

### Specifications:

|                     |                                           |
|---------------------|-------------------------------------------|
| Construction:       | Dual layer Static Dissipative rubber      |
| Material Thickness: | 2mm ( $\pm 5\%$ )                         |
| Colours:            | Grey, Blue, Beige                         |
| Texture:            | Slight emboss                             |
| Weight:             | 2.7kg/m <sup>2</sup>                      |
| Hardness:           | 75 $\pm$ 5 Shore A                        |
| Rp-p Colour Layer:  | 10E6 - 10E8 ohms tested per IEC 61340-2-3 |
| Rp-p Black Layer:   | <10E5 ohms tested per IEC 61340-2-3       |
| Rg Colour Layer:    | 10E6 - 10E8 ohms tested per IEC 61340-2-3 |
| Rg Black Layer:     | <10E5 ohms tested per IEC 61340-2-3       |

**Grounding:** This material must be properly grounded for optimum electrical performance.

**Cleaning:** Use only ESD mat cleaner such as Reztore™ Surface & Mat Cleaner to clean and extend mat useful life. Do not use cleaners containing silicone as silicone will create an insulative film on the surface. Do not use solvent based cleaners as solvents will dry out matting and may cause curling.

*EN 61340-5-1 paragraph 5.2.2 Working surfaces and storage racks  
"All working surfaces and storage racks on which unprotected ESDS may be placed shall be capable of being connected to EPA ground and shall have a point-to-point resistance and resistance to EPA ground in accordance with table 1 (Rp greater or equal to  $1 \times 10^4$ , less than or equal to  $1 \times 10^9$  ohms, and Rg greater or equal to  $7,5 \times 10^5$  to less than or equal to  $1 \times 10^9$  ohms)."*



Tolerances are  $\pm 5$ mm unless specified

Special manufactured items are not returnable for credit

MADE IN BRITAIN

# Vermason

## ROLL, DISSIPATIVE STATFREE DLR RUBBER

VERMASON  
UNIT C, 4TH DIMENSION, FOURTH AVENUE, LETCHWORTH,  
HERTFORDSHIRE, SG6 2TD, UNITED KINGDOM  
PHONE: +44 (0) 1462-672005, FAX: +44 (0) 1462-670440  
E-MAIL: Service@Vermason.co.uk, INTERNET: Vermason.co.uk

DRAWING NUMBER

VER-28214

DATE

August  
2010