

HCMOS 5x3.2mm 1.8V SMD Oscillator



Model: F510L Series

RoHS Compliant / Pb Free

Rev. 5/7/2009

Page 1 of 2

http://www.foxonline.com/need_a_sample.htm

Need a
Sample®

FEATURES

- 1.8V Operation
- HCMOS Output
- Low Power Consumption
- Standby Function
- Tape and Reel (1,000 pcs. STD)

• PART NUMBER SELECTION [Learn More](#) - Internet Required

Part Number	Model Number	Frequency Stability ¹	Operating Temperature (°C)	Frequency Range (MHz)
551-Frequency-xxxxx	F510L	±100PPM	-10 ~ +70	1.800 ~ 125.000
552-Frequency-xxxxx	F510LR	±100PPM	-40 ~ +85	1.800 ~ 125.000
553-Frequency-xxxxx	F515L	±50PPM	-10 ~ +70	1.800 ~ 125.000
554-Frequency-xxxxx	F515LR	±50PPM	-40 ~ +85	1.800 ~ 125.000
555-Frequency-xxxxx	F516L	±25PPM	-10 ~ +70	1.800 ~ 125.000
556-Frequency-xxxxx	F516LR	±25PPM*	-40 ~ +85	1.800 ~ 50.000
557-Frequency-xxxxx	F518L	±20PPM*	-10 ~ +70	1.800 ~ 50.000

• ELECTRICAL CHARACTERISTICS

PARAMETERS	MAX (unless otherwise noted)
Frequency Range (Fo)	1.800 ~ 125.000 MHz
Storage Temperature Range (T _{STG})	-55°C ~ +125°C
Supply Voltage (V _{DD})	1.8V ± 5%
Input Current (I _{DD})	
1.800 ~ 32.100 MHz	7mA
32.100+ ~ 50.000 MHz	15mA
50.000+ ~ 125.000 MHz	25mA
Output Symmetry (50% V _{DD})	40% ~ 60%
Rise Time (20% ~ 80% V _{DD}) (T _R)	
1.800 ~ 32.100 MHz	5nS
32.100+ ~ 125.000 MHz	3.5nS
Fall Time (80% ~ 20% V _{DD}) (T _F)	
1.800 ~ 32.100 MHz	5nS
32.100+ ~ 125.000 MHz	3.5nS
Output Voltage (V _{OL})	20% V _{DD}
(V _{OH})	80% V _{DD} Min
Output Current (I _{OL})	2mA Min
(I _{OH})	2mA Min
Output Load (HCMOS)	15pF
Standby Current	10µA
Start-up Time (T _s)	10mS
Output Disable Time ²	300nS
Output Enable Time ²	10mS


¹ Inclusive of 25°C tolerance, operating temperature range, input voltage change, load change, aging, shock, and vibration. *Excludes Shock/Vibration

² An internal pullup resistor from pin 1 to pin 4 allows active output if pin 1 is left open.

Note: A 0.01µF capacitor should be placed between V_{DD} (Pin 4) and GND (Pin2) to minimize power supply noise.

Drawing is for reference to critical specifications defined by size measurements.

Certain non-critical visual attributes, such as side castellations, reference pin shape, etc. may vary. All specifications subject to change without notice.



• ENABLE / DISABLE FUNCTION

INH (Pin 1)	OUTPUT (Pin 3)
OPEN ²	ACTIVE
'1' Level V _{IH} ≥ 70% V _{DD}	ACTIVE
'0' Level V _{IL} ≤ 30% V _{DD}	High Z

HCMOS 5x3.2mm 1.8V SMD Oscillator



Model: F510L Series

RoHS Compliant / Pb Free

Rev. 5/7/2009

Page 2 of 2

http://www.foxonline.com/need_a_sample.htm


Need a
Sample®

• TAPE SPECIFICATIONS (millimeters)

MODEL	A	B	C	D	E	F	STD Reel QTY
F510L Series	Ø1.5	4.0	8.0	5.5	12.0	1.5	1,000

• REEL SPECIFICATIONS (millimeters)

MODEL	G	H	I	J	K	L	M
F510L Series	2.0	Ø13	Ø21	Ø62	Ø180	13.5	2.0



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Fox:

[F515LR-24.576MHZ](#)