All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of © BERG ELECTRONICS Copyright BERG ELECTRONICS INC.
Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire.
Propriete de © BERG ELECTRONICS. Droits de reproduction BERG ELECTRONICS INC.







PIN NUMBER	DIM X PIN LENGTH
36,67	3.5±0.1
1,17,34 35,51,68	5.0±0.1
ALL OTHERS	4.25±0.1





PIN ASSIGNMENTS

J-1	J-2	J-1	J-2
	1 NC		
1	2	35	36
2	3	36	37
3	4	37	38
4	5	38	39
5	6	39	40
6	7	40	41
7	8	41	42
8	9	42	43
9	10	43	44
10	11	44	45
11	12	45	46
12	13	46	47
13	14	47	48
14	15	48	49
15	16	49	50
16	17	50	51
17	18	51	52
18	19	52	53
19	20	53	54
20	21	54	55
21	22	55	56
22	23	56	57
23	24	57	58
24	25	58	59
25	26	59	60
26	27	60	61
27	28	61	62
28	29	62	63
29	30	63	64
30	31	64	65
31	32	65	66
32	33	66	67
33	34	67	68
34	35	68	69

ltr	ecn no	dr	date
A	V71119	RHG	8/1/97

mat'l. code

tolerances unless otherwise specified
linear .X ±.3 / .XX ±.13 / .XXX ±.051
angles 0° ±2°

dr	R.GRAPE	8/1/97
engr	D.BRANN	8/1/97
chr	D.BRANN	8/1/97
appd	D.BRANN	8/1/97

CUSTOMER COPY
projection
mm
scale 1:1

BERG ELECTRONICS

title: PCMCIA TO CONAN HEADER FLEX ASSY
product family: MCS
size: A4
dwg no: 73625
code: –
sheet: 1 of 2
cage code: 22526

sheet index	revision	A	A
	sheet	1	2

form no. 7530-001-103

PDM: Rev:A STATUS: Released Printed: Oct 12, [illegible]

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of ©BERG ELECTRONICS Copyright BERG ELECTRONICS INC.
Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de ©BERG ELECTRONICS. Droits de reproduction BERG ELECTRONICS INC.

PRODUCT NO.	FLEX LENGTH / MM
73625-20320	24.5
73625-20520	41.5
73625-20820	71.5



RECOMMENDED
CONAN RECEPTACLE
P/N 91930-21169



RECOMMENDED
PAD REQUIREMENT
FOR CONAN RECEPTACLE

NOTES:

1. RECOMMENDED MATING CONNECTOR:
   CONAN RECEPTACLE P/N 91930-21169
2. PCMCIA HEADER:
   MATERIAL: PLASTIC - LCP
   PIN - PHOSPHOR BRONZE
   SEE DRAWING 92140 FOR ADDITIONAL INFORMATION
   PLATING: UNDERPLATING: 0.5 um Ni
   CONTACT AREA: 0.1 um Au
   OVER 0.5 um Pd-Ni
3. CONAN HEADER:
   MATERIAL: PLASTIC - LCP
   PIN - PHOSPHOR BRONZE
   SEE DRAWING 91900 FOR ADDITIONAL INFORMATION
   PLATING: UNDERPLATING: 1.27 um Ni
   CONTACT AREA: .38 um GXT
   SOLDERTAILS: 2.5 um Sn-Pb

ltr	ecn no	dr	date
A			

mat'l. code

tolerances unless otherwise specified
linear .X ±.3
.XX ±.13
.XXX ±.051
angles 0° ±2°

dr	R.GRAPE	8/1/97
engr	D.BRANN	8/1/97
chr	D.BRANN	8/1/97
appd	D.BRANN	8/1/97

CUSTOMER COPY
projection
mm
scale 1:1

BERG ELECTRONICS

title: PCMCIA TO CONAN HEADER FLEX ASSY
product family: MCS
code: –
size: A4
dwg no: 73625
sheet: 2 of 2
cage code: 22526

sheet index | revision sheet

form no. 7530-001-103

PDM: Rev:A STATUS:Released Printed: Oct 12, 2010