








- 1 PHYSICAL PROPERTIES (STANDARD)
HOUSING: POLYESTER, UL 94V-0 RATED, COLOR: GRAY.
TUBULAR CONTACT: COPPER ALLOY, ZINC PLATED.
SCREW: STEEL, ZINC PLATED CLEAR CHROMATE.
- 2 PHYSICAL PROPERTIES (DURAMAX)
HOUSING: POLYESTER, UL 94V-0 RATED, COLOR: GRAY.
TUBULAR CONTACT: COPPER ALLOY, NICKEL PLATED.
SCREW: COPPER ALLOY, NICKEL PLATED.
3. MECHANICAL
PITCH: .375
MOUNTING: DIRECT MOUNT OR MINIATURE CHANNEL AND CLAMP.
OPERATING TEMPERATURE: 150°C MAX.
TORQUE: RECOMMENDED TIGHTENING TORQUE IS 8 IN-LBS.
4. ELECTRICAL
MAXIMUM CURRENT: 50A
OPERATING VOLTAGE: 600 V
WIRE RANGE: 8-22 AWG.
- 5 SEE RESTRICTED CUSTOMER DRAWING 4-1437394-3.

-	4-1437394-3	5
2	1546147-2	
1	1546147-1	
MATERIAL / FINISH		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WELDON	15JAN2002	 TE Connectivity			
		CHK S. YODER	15JAN2002				
DIMENSIONS: INCHES		APVD S. YODER	15JAN2002	NAME ASSEMBLY, TERMINAL BLOCK, NEMA, FLAT BASE, MEDIUM DUTY, TUBULAR SCREW			
		PRODUCT SPEC -					
		APPLICATION SPEC -		SIZE A2	CAGE CODE 00779	DRAWING NO C-1546147	RESTRICTED TO -
MATERIAL SEE TABLE		WEIGHT -		SCALE 3:1			
				SHEET 1		OF 1	
				REV E			