


© 1967 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP
PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.



FOR .102 TO .214 WIRE INSULATION DIA.
TONGUE MATERIAL THK. = .040 ±.002

REVISIONS

ZONE	LTR	DESCRIPTION	DATE	APPROVED
B		REDRAWN & REV P-6077	7-30-69	FLY
C		REVISED PC-5579	10-8-70	me
D		REVISED PC-5578		
E		REV / 0610-0094-98	2-4-99	SH
E1		REV PER ELP 05-013140	10/20/05	VR/TM

1	WIRE TERMINAL	50848	BODY: COPPER (ASTM B152) NICKEL PLATE (QQ-N-290) .0003 AVG. EXT. THK.	
			SLEEVE: COPPER (ASTM B152) NICKEL PL (QQ-N-290). 00003 AVG. EXT. THK.	
			INSULATION: TEFLON (ASTM D3295) COLOR: BLACK	
QTY	DESCRIPTION	PART NO.	MATERIAL & FINISH	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON: DECIMALS ±.008 ANGLES ± 5°		CONTRACT NO. H	AMP INCORPORATED HARRISBURG, PENNSYLVANIA	
MATERIAL		DR. <i>Steve Kaut</i> 7-29-69	NAME WIRE TERMINAL	
SEE TABLE		CHK. <i>P. J. Young</i> 7-30-69	PIDG™ STRATO-THERM-RING TONGUE	
		APPD. <i>W. J. Wabel</i> 8-6-69	WIRE SIZE: 12-10	
		REL. <i>J. M. Ensminger</i> 8-6-69		
		DSGN APPD.	SIZE B	CODE IDENT NO. 00779
		OTHER APPD.	SCALE NTS	NUMBER 50848
			SHEET 10F1	