






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
J	—		B1	REVISED PER ECR-10-019980	04OCT10	HMR	TM



TABLE


②	ヘッダーハウジング HDR HOUSING	6/6ナイロンガラス強化UL94V-0 6/6NYLON GRASS FILLED UL94V-0
①	ポストコンタクト POST CONTACT	錫めっき仕上げ 黄銅 BRASS TIN PLATED
NO.	名前 (NAME)	材料 (MATERIAL)

P.C.B. LAYOUT ON RECOMMENDATION



- 注
- 取付穴寸法
 - 適応基板厚 : 1.6t
 - かん合相手型番 : プラグハウジング : SEE TABLE

- NOTES
- RECOMMENDED P.C.B LAYOUT
 - APPLICABLE P.C.B THICKNESS :1.6t
 - MATING CONN. P/N PLUG HOUSING : SEE TABLE



パンチ加工 (PUNCHED HOLE)	0.7 ^{+0.1} ₋₀
ドリル加工 (DRILLED HOLE)	0.8 ±0.05
	A 寸法 DIM. A

2-1939984-3	TYPE C	青色 BLUE	2-1939983-3
1939984-1	TYPE A	自然色 NATURAL	1939983-1
かん合相手型番 MATING CONN. P/N	キーイング形状 TYPE OF KEYING	色調 COLOR	型番 PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.SATO	13OCT2006	Tyco Electronics Tyco Electronics AMP K.K. Kawasaki, Japan	
		CHK N.YAMASAKI	13OCT2006		
		APVD N.YAMASAKI	13OCT2006	NAME 名称 GRACE INERTIA CONNECTOR 3.3 HEADER ASSEMBLY 10POS 2ROW	
		PRODUCT SPEC 製品規格 108-78231			
		APPLICATION SPEC 取付適用規格 114-5372			
		WEIGHT		SIZE A3	CAGE CODE 00779
		CUSTOMER DRAWING		DRAWING NO 番号 1939983	RESTRICTED TO —
				SCALE 尺度 NONE	SHEET 1 OF 2
					REV B1

キंक形状 KINK FORM	A	S	S	S	A	B	S	S	S	B
回路番号 CIRCUIT NO.	1	2	3	4	5	6	7	8	9	10

4


3

2


1

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
J	—		—	SEE SHEET 1	—	—

キーイングタイプ
TYPE OF KEYING



TYPE A



TYPE C

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 寸
mm

MATERIAL
材料
SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:
一般公差

0 PLC ± 0.3
1 PLC ± 0.3
2 PLC ± 0.3
3 PLC ±
4 PLC ±
ANGLES ±
FINISH
仕上

DWN
—
CHK
—
APVD
—

PRODUCT SPEC
製品規格
—

APPLICATION SPEC
取付適用規格

WEIGHT

Tyco Electronics
Kawasaki, Japan

NAME
名称
GRACE INERTIA CONNECTOR 3.3
HEADER ASSEMBLY 10POS 2ROW

SIZE
A3

CAGE CODE
00779

DRAWING NO
番号
C- 1939983

RESTRICTED TO
—

CUSTOMER DRAWING

SCALE
尺度
NONE

SHEET
2 OF 2

REV
B1

AMP 1470-19 REV 31MAR2000