



FCIconnect.com

Copyright FCI.

1

2

List of "SFW__R-1/2STE1LF" customer document

DOCUMENT NO.	LIST
SC-SFW10	SPEC.
JSA95854	CAT.NO.TABLE FOR 1mm SPACING SMT CONNECTOR (SFW__R-1/2ST__LF)
JSA95855	1mm SPACING SMT CONNECTOR (SFW__R-1ST__LF)
JSA95856	1mm SPACING SMT CONNECTOR (SFW__R-2ST__LF)
JSA95857	CAT.NO.TABLE FOR PLASTIC TAPE PACKAGED 1mm SPACING SMT CONNECTOR (SFW__R-1/2STE1LF)
JSA95858	PLASTIC TAPE PACKAGED 1mm SPACING SMT CONNECTOR (SFW__R-1STE1LF)
JSA95859	PLASTIC TAPE PACKAGED 1mm SPACING SMT CONNECTOR (SFW__R-2STE1LF)
JSA91605	RECOMMENDED CABLE (FPC) (SFW__R-1/2ST__)
JSA91604	RECOMMENDED CABLE (FFC) (SFW__R-1/2ST__)
GS-20-129	HANDLING PROCEDURES

mat'l. code -				surface ISO 1302 58 ✓ tolerance ISO 406 ISO 1101		projection 		product family 58RF		CODE JP	
ltr				ecn no		dr		date		title	
A				J05-0055		H.T		'05/2/4		1mm SPACING FPC/FFC CONNECTOR DOCUMENT LIST	
B				J06-0398		H.T		9/26/'06		(Cat. No. : SFW__R-1/2STE1LF)	
C				J09-0358		M.Y		2009-10-5			
D				J09-0380		M.Y		2009-10-27			
										dwg no	
										sheet 1 of 1	
										size	
										A4	
										type	
										Product Customer Drawing	
sheet index				revision sheet		D 1				Rev. D	

form: A4

1

2

PDM: Rev:D

STATUS: Released

Printed: Nov 01, 2009

CAT. NO. & DIMENSIONS

NO. OF CONTACTS (n)	CAT. NO.	DIMENSIONS (NOTE2)			
		A ± 0.2	B ± 0.2	C ± 0.2	D ± 0.1
4	SFW4R-1/2ST__LF	9.8	8.6	3.0	5.3
5	SFW5R-1/2ST__LF	10.8	9.6	4.0	6.3
6	SFW6R-1/2ST__LF	11.8	10.6	5.0	7.3
7	SFW7R-1/2ST__LF	12.8	11.6	6.0	8.3
8	SFW8R-1/2ST__LF	13.8	12.6	7.0	9.3
9	SFW9R-1/2ST__LF	14.8	13.6	8.0	10.3
10	SFW10R-1/2ST__LF	15.8	14.6	9.0	11.3
11	SFW11R-1/2ST__LF	16.8	15.6	10.0	12.3
12	SFW12R-1/2ST__LF	17.8	16.6	11.0	13.3
13	SFW13R-1/2ST__LF	18.8	17.6	12.0	14.3
14	SFW14R-1/2ST__LF	19.8	18.6	13.0	15.3
15	SFW15R-1/2ST__LF	20.8	19.6	14.0	16.3
16	SFW16R-1/2ST__LF	21.8	20.6	15.0	17.3
17	SFW17R-1/2ST__LF	22.8	21.6	16.0	18.3
18	SFW18R-1/2ST__LF	23.8	22.6	17.0	19.3
19	SFW19R-1/2ST__LF	24.8	23.6	18.0	20.3
20	SFW20R-1/2ST__LF	25.8	24.6	19.0	21.3
21	SFW21R-1/2ST__LF	26.8	25.6	20.0	22.3
22	SFW22R-1/2ST__LF	27.8	26.6	21.0	23.3
23	SFW23R-1/2ST__LF	28.8	27.6	22.0	24.3
24	SFW24R-1/2ST__LF	29.8	28.6	23.0	25.3
25	SFW25R-1/2ST__LF	30.8	29.6	24.0	26.3
26	SFW26R-1/2ST__LF	31.8	30.6	25.0	27.3
27	SFW27R-1/2ST__LF	32.8	31.6	26.0	28.3
28	SFW28R-1/2ST__LF	33.8	32.6	27.0	29.3
29	SFW29R-1/2ST__LF	34.8	33.6	28.0	30.3
30	SFW30R-1/2ST__LF	35.8	34.6	29.0	31.3

CAT. NO.

SFW (n) R - 1 ST __ LF

SERIES NAME

NO. OF CONTACTS

RIGHT ANGLE TYPE

FOR FPC/FFC, CONTACT DIRECTION

1. LOWER CONTACT TYPE
2. UPPER CONTACT TYPE

FOR AUTOMATIC MOUNTING (SMT)

PACKAGE STYLE

LEAD FREE

NOTES

1. THIS PRODUCT IS THE CONNECTOR USED FOR FPC/FFC AND COPS WITH AUTOMATIC MOUNTING (SMT).


2. SEE PART DRAWINGS FOR DIMENSIONS A~D.

3. A  SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

mat'l. code				surface 58 / tolerance ISO 1302 ISO 406 ISO 1101			projection 			product family 58RF						CODE JP			
ltr	ecn no	dr	date	tolerances unless otherwise specified									title CAT. NO. TABLE FOR 1mm SPACING SMT CONNECTOR (Cat. No. SFW__R-1/2ST__LF)						
AA	J05-0055	H.T	05-02-04	angles	linear														
AB	J06-0398	H.T	06-09-26																
AC	S08-0276	DGOH	08-08-22				scale 			dwg no sheet 1 of 1 JSA 95854 size A4									
				dr	H. TAKAKURA		06-09-26												
				enrg	H. TAKAKURA		06-09-26												
				chr	DENNIS GOH		08-08-22												
				appd	JOEY NG		08-08-22												
sheet index		revision	AC															Rev. AC	
		sheet	1																

SC-SFW10 JSA95855 95856 95857 95858 95859 91605 91604 1

1										2																																																																																																																																																																																																													
<table border="1"><thead><tr><th>PT. NO.</th><th>PARTS NAME</th><th>MATERIAL</th><th>Q'TY</th><th>NOTE</th></tr></thead><tbody><tr><td>1</td><td>HOUSING</td><td>PPS RESIN GLASS REINFORCED (UL94V-0)</td><td>1</td><td>COLOR : BROWN</td></tr><tr><td>2</td><td>SLIDER</td><td>PPS RESIN GLASS REINFORCED (UL94V-0)</td><td>1</td><td>COLOR : BLACK</td></tr><tr><td>3</td><td>CONTACT</td><td rowspan="2">PHOSPHOR BRONZE</td><td>n</td><td rowspan="2">PLATING : TIN</td></tr><tr><td>4</td><td>MOUNTING PLATE</td><td>2</td></tr></tbody></table>																				PT. NO.	PARTS NAME	MATERIAL	Q'TY	NOTE	1	HOUSING	PPS RESIN GLASS REINFORCED (UL94V-0)	1	COLOR : BROWN	2	SLIDER	PPS RESIN GLASS REINFORCED (UL94V-0)	1	COLOR : BLACK	3	CONTACT	PHOSPHOR BRONZE	n	PLATING : TIN	4	MOUNTING PLATE	2																																																																																																																																																																													
PT. NO.	PARTS NAME	MATERIAL	Q'TY	NOTE																																																																																																																																																																																																																			
1	HOUSING	PPS RESIN GLASS REINFORCED (UL94V-0)	1	COLOR : BROWN																																																																																																																																																																																																																			
2	SLIDER	PPS RESIN GLASS REINFORCED (UL94V-0)	1	COLOR : BLACK																																																																																																																																																																																																																			
3	CONTACT	PHOSPHOR BRONZE	n	PLATING : TIN																																																																																																																																																																																																																			
4	MOUNTING PLATE		2																																																																																																																																																																																																																				
n : NO. OF CONTACTS NOTES 1. THIS PRODUCT IS THE CONNECTOR USED FOR FPC/FFC AND CYPES WITH AUTOMATIC MOUNTING (SMT). 2. FLATNESS FOR CONTACT TERMINAL HOUSING MUST BE WITHIN TOLERANCE IN Z PORTION DETAILED DRAWING. 3. THIS PRODUCT IS LOWER CONTACT TYPE CONNECTOR. 4. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008 5. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A REFLOW SOLDERING OVEN. 3. A SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING. REVISION.																																																																																																																																																																																																																							
RECOMMENDED PC BOARD LAYOUT (COMPONENT SIDE)																																																																																																																																																																																																																							
<table border="1"><thead><tr><th colspan="4">mat'l. code</th><th colspan="2">surface 58</th><th colspan="2">tolerance ISO 1302</th><th colspan="2">projection</th><th colspan="2">product family 58RF</th><th colspan="2">CODE JP</th></tr><tr><th colspan="4"></th><th colspan="2">ISO 406</th><th colspan="2">ISO 1101</th><th colspan="2"></th><th colspan="2"></th><th colspan="2"></th></tr><tr><th colspan="4"></th><th colspan="2">tolerances unless otherwise specified</th><th colspan="2">±0.2</th><th colspan="2">mm</th><th colspan="2">title</th><th colspan="2"></th></tr><tr><th colspan="4"></th><th colspan="2">linear</th><th colspan="2"></th><th colspan="2">scale</th><th colspan="2">1mm SPACING SMT CONNECTOR (Cat. No. SFW__R-1ST__LF)</th><th colspan="2"></th></tr></thead><tbody><tr><td>ltr</td><td>ecn no</td><td>dr</td><td>date</td><td colspan="2">angles</td><td colspan="2"></td><td colspan="2"></td><td colspan="2">dwg no</td><td colspan="2">sheet 1 of 1</td></tr><tr><td>AA</td><td>J04-0180</td><td>H.T</td><td>04-07-02</td><td colspan="2"></td><td colspan="2"></td><td colspan="2"></td><td colspan="2">JSA 95855</td><td colspan="2">size A4</td></tr><tr><td>AB</td><td>J05-0055</td><td>H.T</td><td>05-02-04</td><td colspan="2"></td><td colspan="2"></td><td colspan="2"></td><td colspan="2"></td><td colspan="2"></td></tr><tr><td>AC</td><td>J05-0736</td><td>H.T</td><td>05-10-28</td><td colspan="2"></td><td colspan="2"></td><td colspan="2"></td><td colspan="2"></td><td colspan="2"></td></tr><tr><td>AD</td><td>J06-0398</td><td>H.T</td><td>06-09-26</td><td>dr</td><td>H. TAKAKURA</td><td colspan="2">06-09-26</td><td colspan="2"></td><td colspan="2"></td><td colspan="2"></td></tr><tr><td>AE</td><td>S08-0276</td><td>DGOH</td><td>08-08-22</td><td>enr</td><td>H. TAKAKURA</td><td colspan="2">06-09-26</td><td colspan="2"></td><td colspan="2"></td><td colspan="2"></td></tr><tr><td></td><td></td><td></td><td></td><td>chr</td><td>DENNIS GOH</td><td colspan="2">08-08-22</td><td colspan="2"></td><td colspan="2"></td><td colspan="2"></td></tr><tr><td></td><td></td><td></td><td></td><td>appd</td><td>JOEY NG</td><td colspan="2">08-08-22</td><td colspan="2"></td><td colspan="2"></td><td colspan="2"></td></tr><tr><td colspan="4">sheet index</td><td colspan="2">revision</td><td colspan="2">AE</td><td colspan="2"></td><td colspan="2">type</td><td colspan="2">Product Customer Drawing</td></tr><tr><td colspan="4">1</td><td colspan="2">1</td><td colspan="2"></td><td colspan="2"></td><td colspan="2"></td><td colspan="2">Rev. AE</td></tr></tbody></table>																				mat'l. code				surface 58		tolerance ISO 1302		projection		product family 58RF		CODE JP						ISO 406		ISO 1101												tolerances unless otherwise specified		±0.2		mm		title								linear				scale		1mm SPACING SMT CONNECTOR (Cat. No. SFW__R-1ST__LF)				ltr	ecn no	dr	date	angles						dwg no		sheet 1 of 1		AA	J04-0180	H.T	04-07-02							JSA 95855		size A4		AB	J05-0055	H.T	05-02-04											AC	J05-0736	H.T	05-10-28											AD	J06-0398	H.T	06-09-26	dr	H. TAKAKURA	06-09-26								AE	S08-0276	DGOH	08-08-22	enr	H. TAKAKURA	06-09-26												chr	DENNIS GOH	08-08-22												appd	JOEY NG	08-08-22								sheet index				revision		AE				type		Product Customer Drawing		1				1								Rev. AE	
mat'l. code				surface 58		tolerance ISO 1302		projection		product family 58RF		CODE JP																																																																																																																																																																																																											
				ISO 406		ISO 1101																																																																																																																																																																																																																	
				tolerances unless otherwise specified		±0.2		mm		title																																																																																																																																																																																																													
				linear				scale		1mm SPACING SMT CONNECTOR (Cat. No. SFW__R-1ST__LF)																																																																																																																																																																																																													
ltr	ecn no	dr	date	angles						dwg no		sheet 1 of 1																																																																																																																																																																																																											
AA	J04-0180	H.T	04-07-02							JSA 95855		size A4																																																																																																																																																																																																											
AB	J05-0055	H.T	05-02-04																																																																																																																																																																																																																				
AC	J05-0736	H.T	05-10-28																																																																																																																																																																																																																				
AD	J06-0398	H.T	06-09-26	dr	H. TAKAKURA	06-09-26																																																																																																																																																																																																																	
AE	S08-0276	DGOH	08-08-22	enr	H. TAKAKURA	06-09-26																																																																																																																																																																																																																	
				chr	DENNIS GOH	08-08-22																																																																																																																																																																																																																	
				appd	JOEY NG	08-08-22																																																																																																																																																																																																																	
sheet index				revision		AE				type		Product Customer Drawing																																																																																																																																																																																																											
1				1								Rev. AE																																																																																																																																																																																																											
SC_SFW10 JSA95854 form: A4 1 2																																																																																																																																																																																																																							




PT. NO.	PARTS NAME	MATERIAL	Q'TY	NOTE
1	HOUSING	PPS RESIN GLASS REINFORCED (UL94V-0)	1	COLOR : BROWN
2	SLIDER	PPS RESIN GLASS REINFORCED (UL94V-0)	1	COLOR : BLACK
3	CONTACT	PHOSPHOR BRONZE	n	PLATING : TIN
4	MOUNTING PLATE		2	

n : NO. OF CONTACTS

NOTES

1. THIS PRODUCT IS THE CONNECTOR USED FOR FPC/FFC AND COPEs WITH AUTOMATIC MOUNTING (SMT).
2. FLATNESS FOR CONTACT TERMINAL HOUSING MUST BE WITHIN TOLERANCE IN Z PORTION DETAILED DRAWING.
3. THIS PRODUCT IS UPPER CONTACT TYPE CONNECTOR.
4. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER?COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
5. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A REFLOW SOLDERING OVEN.
6. A $\triangle$ AE SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

RECOMMENDED PC BOARD LAYOUT (COMPONENT SIDE)



mat'l. code				surface 58	tolerance ISO 1302	projection	product family 58RF	CODE JP
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title 1mm SPACING SMT CONNECTOR (Cat. No. SFW__R-2ST__LF)	
AA	J04-0180	H.T	04-07-02	angles	linear			
AB	J05-0055	H.T	05-02-04			scale	dwg no sheet 1 of 1 size	
AC	J05-0736	H.T	05-10-28					
AD	J06-0398	H.T	06-09-26	dr	H. TAKAKURA	06-09-26	JSA 95856	
AE	S08-0276	DGOH	08-08-22	enr	H. TAKAKURA	06-09-26		
				chr	DENNIS GOH	08-08-22	type Product Customer Drawing	
				appd	JOEY NG	08-08-22		
sheet index	revision	AE					Rev. AE	
	sheet	1						

SC_SFW10 JSA95854
form: A4

CAT. NO. & DIMENSIONS

NO. OF CONTACTS (n)	CAT. NO. (NOTE2)	DIMENSIONS (NOTE3)		
		E ± 5	F ± 0.3	G ± 0.1
4	SFW4R-1/2STE1 LF	20.4	16	—
5	SFW5R-1/2STE1 LF	28.4	24	—
6	SFW6R-1/2STE1 LF	28.4	24	—
7	SFW7R-1/2STE1 LF	28.4	24	—
8	SFW8R-1/2STE1 LF	28.4	24	—
9	SFW9R-1/2STE1 LF	28.4	24	—
10	SFW10R-1/2STE1 LF	28.4	24	—
11	SFW11R-1/2STE1 LF	28.4	24	—
12	SFW12R-1/2STE1 LF	28.4	24	—
13	SFW13R-1/2STE1 LF	36.4	32	28.4
14	SFW14R-1/2STE1 LF	36.4	32	28.4
15	SFW15R-1/2STE1 LF	36.4	32	28.4
16	SFW16R-1/2STE1 LF	36.4	32	28.4
17	SFW17R-1/2STE1 LF	48.4	44	40.4
18	SFW18R-1/2STE1 LF	48.4	44	40.4
19	SFW19R-1/2STE1 LF	48.4	44	40.4
20	SFW20R-1/2STE1 LF	48.4	44	40.4
21	SFW21R-1/2STE1 LF	48.4	44	40.4
22	SFW22R-1/2STE1 LF	48.4	44	40.4
23	SFW23R-1/2STE1 LF	48.4	44	40.4
24	SFW24R-1/2STE1 LF	48.4	44	40.4
25	SFW25R-1/2STE1 LF	48.4	44	40.4
26	SFW26R-1/2STE1 LF	48.4	44	40.4
27	SFW27R-1/2STE1 LF	48.4	44	40.4
28	SFW28R-1/2STE1 LF	60.4	56	52.4
29	SFW29R-1/2STE1 LF	60.4	56	52.4
30	SFW30R-1/2STE1 LF	60.4	56	52.4

CAT. NO.

SFW (n) R - 1 ST E1 LF

SERIES NAME

NO. OF CONTACTS

RIGHT ANGLE TYPE

FOR FPC/FFC, CONTACT DIRECTION

1. LOWER CONTACT TYPE
2. UPPER CONTACT TYPE



FOR AUTOMATIC MOUNTING (SMT)

TAPE PACKAGING

LEAD FREE


NOTES

1. THIS PRODUCT IS THE CONNECTOR USED FOR FPC/FFC AND COPELS WITH AUTOMATIC MOUNTING (SMT).
2. THIS CATALOG NO. INDICATES PLASTIC TAPE PACKAGED CONNECTOR.
3. SEE PART DRAWINGS FOR DIMENSIONS E~G.
4. A  SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

mat'l. code				surface 58/ISO 1302	tolerance ISO 406/ISO 1101	projection 	product family 58RF	CODE JP
ltr	ecn no	dr	date	tolerances unless otherwise specified			title CAT. NO. TABLE FOR PLASTIC TAPE PACKAGED 1mm SPACING SMT CONNECTOR (Cat. No. SFW__R-1/2STE1 LF)	
AA	J05-0055	H.T	05-02-04	angles	linear			
AB	J06-0398	H.T	06-09-26			scale 	dwg no JSA 95857 sheet 1 of 1 size A4	
AC	S08-0276	DGOH	08-08-22					
				dr	H. TAKAKURA	06-09-26	type Product Customer Drawing	
				enr	H. TAKAKURA	06-09-26		
				chr	DENNIS GOH	08-08-22		
				appd	JOEY NG	08-08-22		
sheet index	revision	AC						Rev. AC

SC_SFW10 JSA95854 95858 95859
form: A4

1										2																																							
CONNECTOR PACKAGING STYLE																																																	
<table><thead><tr><th>PT. NO.</th><th>PARTS NAME</th><th>CAT. NO.</th><th>MATERIAL</th><th>Q'TY</th><th>NOTE</th></tr></thead><tbody><tr><td>1</td><td>REEL</td><td>_____</td><td>CARDBOARD</td><td>1</td><td>COLOR:WHITE/GREY</td></tr><tr><td>2</td><td>PLASTIC (EMBOSS) TAPE</td><td>_____</td><td>PET</td><td>_____</td><td>COLOR:TRANSPARENCY</td></tr><tr><td>3</td><td>COVER</td><td>_____</td><td>POLYESTER</td><td>_____</td><td>COLOR:TRANSPARENCY</td></tr><tr><td>4</td><td>CONNECTOR</td><td>SFW__R-1ST__LF</td><td>SEE ATTACHED DWG.</td><td>2000</td><td>LOWER CONTACT TYPE</td></tr></tbody></table>																				PT. NO.	PARTS NAME	CAT. NO.	MATERIAL	Q'TY	NOTE	1	REEL	_____	CARDBOARD	1	COLOR:WHITE/GREY	2	PLASTIC (EMBOSS) TAPE	_____	PET	_____	COLOR:TRANSPARENCY	3	COVER	_____	POLYESTER	_____	COLOR:TRANSPARENCY	4	CONNECTOR	SFW__R-1ST__LF	SEE ATTACHED DWG.	2000	LOWER CONTACT TYPE
PT. NO.	PARTS NAME	CAT. NO.	MATERIAL	Q'TY	NOTE																																												
1	REEL	_____	CARDBOARD	1	COLOR:WHITE/GREY																																												
2	PLASTIC (EMBOSS) TAPE	_____	PET	_____	COLOR:TRANSPARENCY																																												
3	COVER	_____	POLYESTER	_____	COLOR:TRANSPARENCY																																												
4	CONNECTOR	SFW__R-1ST__LF	SEE ATTACHED DWG.	2000	LOWER CONTACT TYPE																																												
NOTES																																																	
1. THIS IS PLASTIC TAPE PACKAGED CONNECTOR USED FOR FPC/FFC AND CYPES WITH AUTOMATIC MOUNTING (SMT).																																																	
2. SEE JIS C 0806 (PACKING OF ELECTRONIC COMPONENTS ON CONTINUOUS TAPES (SURFACE MOUNTING DEVICES)) FOR SHAPE AND DIMENSIONS OF PLASTIC (EMBOSS) TAPE AND REEL.																																																	
3. E DIMENSION IS PORTION OF THE CORE.																																																	
4. A SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.																																																	
mat'l. code										surface 58 / tolerance ISO 1302		projection		product family 58RF		CODE JP																																	
ltr ecn no dr date										tolerances unless otherwise specified				title																																			
AA J05-0055 H.T 05/02/04										angles linear ±5		mm		PLASTIC TAPE PACKAGED																																			
AB J06-0398 H.T 06/09/26										±5°		scale X		1mm SPACING SMT CONNECTOR																																			
AC S08-0276 DGOH 08-08-22										dr H. TAKAKURA 06-09-26		FCI		(Cat. No. SFW__R-1STE1 LF)																																			
										engr H. TAKAKURA 06-09-26				dwg no sheet 1 of 1 size																																			
										chr DENNIS GOH 08-08-22				JSA 95858 A4																																			
										appd JOEY NG 08-08-22				type Product Customer Drawing																																			
sheet index		revision sheet		AC 1														Rev. AC																															
SC_SFW10 JSA95857										form: A4																																							
1										2																																							



PT. NO.	PARTS NAME	CAT. NO.	MATERIAL	Q'TY	NOTE
1	REEL	_____	CARDBOARD	1	COLOR:WHITE/GREY
2	PLASTIC (EMBOSS) TAPE	_____	PET	_____	COLOR:TRANSPARENCY
3	COVER	_____	POLYESTER	_____	COLOR:TRANSPARENCY
4	CONNECTOR	SFW__R-2ST__LF	SEE ATTACHED DWG.	2000	UPPER CONTACT TYPE


NOTES

- THIS IS PLASTIC TAPE PACKAGED CONNECTOR USED FOR FPC/FFC AND CYPES WITH AUTOMATIC MOUNTING (SMT).
- SEE JIS C 0806 (PACKING OF ELECTRONIC COMPONENTS ON CONTINUOUS TAPES (SURFACE MOUNTING DEVICES)) FOR SHAPE AND DIMENSIONS OF PLASTIC (EMBOSS) TAPE AND REEL.
- E DIMENSION IS PORTION OF THE CORE.
- A  SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

mat'l. code				surface 58 / tolerance ISO 1302 / ISO 406 / ISO 1101	projection	product family 58RF	CODE JP
ltr	ecn no	dr	date	tolerances unless otherwise specified	mm	title PLASTIC TAPE PACKAGED 1mm SPACING SMT CONNECTOR (Cat. No. SFW__R-2STE1 LF)	
AA	J05-0055	H.T	05-02-04	angles			
AB	J06-0398	H.T	06-09-26	linear	scale	dwg no sheet 1 of 1 size JSA 95859 A4	
AC	S08-0276	DGOH	08-08-22	±5°			
				dr	H. TAKAKURA	06-09-26	
				enr	H. TAKAKURA	06-09-26	
				chr	DENNIS GOH	08-08-22	
				appd	JOEY NG	08-08-22	
sheet index	revision	AC				type Product Customer Drawing	
	sheet	1					Rev. AC

RECOMMENDED CABLE (FPC)

n : NO. OF CONDUCTOR



PT. NO.	PARTS NAME	MATERIAL	THICKNESS (μm)
1	BASE FILM	POLYIMIDE OR POLYESTER OR EQUAL	25
2	CONDUCTOR	COPPER FOIL(PLATING:SOLDER 1μm MIN.)	35
3	OVERLAY	POLYIMIDE OR POLYESTER OR EQUAL	—
4	SUPPORTING TAPE	POLYESTER OR POLYIMIDE OR EQUAL	188


NOTES

1. NO BURR AT EACH PORTION.
2. NO PEELING IN COMMON USE.
3. TOTAL THICKNESS LIMIT OF EACH MATERIAL (INCLUDING ADHESIVE AGENT) IS SPECIFIED.
4. A  SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

mat'l. code				surface 58/ISO 1302		tolerance ISO 406 ISO 1101		projection		product family 58RF		CODE JP	
ltr				ecn no		dr		date		title			
AA				J05-0055		H.T		05-02-04		RECOMMENDED CABLE			
AB				J06-0398		H.T		06-09-26		(Cat. No. SFW__R-1/2__)			
AC				S08-0276		DGOH		08-08-22		scale			
				dr		H. TAKAKURA		06-09-26		dwg no		sheet 1 of 1	
				enr		H. TAKAKURA		06-09-26		JSA 91605		A4	
				chr		DENNIS GOH		08-08-22		type		Product Customer Drawing	
				appd		JOEY NG		08-08-22					
sheet index		revision		AC								Rev. AC	
		sheet		1									

RECOMMENDED CABLE (FFC)



n : NO. OF CONDUCTOR



PT. NO.	PARTS NAME	MATERIAL	NOTE
1	INSULATOR	FLAME RESISTING POLYESTER OR EQUAL	_____
2	CONDUCTOR	COPPER FOIL	PLATING:TIN OR SOLDER 1um MIN.
3	SUPPORTING TAPE	FLAME RESISTING POLYESTER OR EQUAL	_____

NOTES

1. NO BURR AT EACH PORTION.
2. NO PEELING IN COMMON USE.
3. A  SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

mat'l. code				surface 58/ISO 1302	tolerance ISO 406 ISO 1101	projection 	product family 58RF	CODE JP
ltr	ecn no	dr	date	tolerances unless otherwise specified			title RECOMMENDED CABLE (Cat. No. SFW__R-1/2__)	
AA	J05-0055	H.T	05-02-04	angles	linear			
AB	J06-0398	H.T	06-09-26			mm	dwg no sheet 1 of 1 size	
AC	S08-0276	DGOH	08-08-22			scale 		
				dr	H. TAKAKURA	06-09-26	JSA 91604	
				enr	H. TAKAKURA	06-09-26		
				chr	DENNIS GOH	08-08-22	type Product Customer Drawing	
				appd	JOEY NG	08-08-22		
sheet index	revision sheet	AC	1					Rev. AC