

ADAPTERS, In-SERIES

Type N, DC -18 GHz, Bulkhead Mount

SPECIFICATIONS:

Models: 5208, 5215

RoHS
Compliant


AEROFLEX
A passion for performance.

Electrical:

Frequency Range _____ DC - 18.0 GHz
VSWR _____ 1.15:1 Max.
Nominal Impedance _____ 50 Ohms
Operating Temp Range _____ -65°C to +125°C

Mechanical:

Connectors _____ Passivated Stainless Steel
Mates with MIL-STD-348
Conductors _____ Gold Plated Beryllium Copper
Nut & Washer: _____ Passivated Stainless Steel
O-Ring _____ Silicone Rubber




Recommended Panel Configuration

Model Number: **5208**

No O-Ring added

Model Number: **5215**

With O-Ring Added



Panel Nut, Lock Washer & O-Ring are Shipped Unassembled

Note: Dimensions in Brackets are Expressed in Millimeters and are for Reference Only.

5208: REV D

AEROFLEX
INMET

Aeroflex / Inmet, Inc. • 300 Dino Drive, Ann Arbor, MI 48103 • U.S.A.
888-244-6638 or 734-426-5553 • FAX: 734-426-5557
www.aeroflex.com/inmet • inmetsales@aeroflex.com