




SECT. F-F
(SCALE 3-1)

- ## NOTES

1. MATERIAL HEADER & EJECT LEVER : G.F. 15% PBTP (UL94V-0)
 PINS : BRASS, SIZE--- □0.635(.025 SQ.)
 SPRING PIN : STEEL
2. MATES WITH MOLEX CONNECTOR SERIES OF 5320.
3. LEGEND

5578 - N B * - *

BASE NUMBER _____
CIRCUIT SIZE _____
WITH EJECT LEVER _____
PLATING CODE OF PIN _____

MATERIAL COLOR
BLANK : BLACK
GY : GREY

	CODE:*	△ MARK COLOR	CONTACT AREA	SOLDER AREA	UNDER PLATE
LEAD-FREE	G1	WHITE	GOLD 0.1μm,000004MIN.		NICKEL 1μm,00004MIN.
LEAD-FREE	G2	ORANGE	GOLD 0.76μm,00003MIN.		
LEAD-FREE	G3	GREEN	GOLD 0.25μm,00001MIN.		
	GS1	YELLOW	GOLD 0.1μm,000004MIN.	TN-LEAD 3μm,00012MIN.	
	GS2	BROWN	GOLD 0.76μm,00003MIN.		
	GS3	BLUE	GOLD 0.25μm,00001MIN.		
LEAD-FREE	T2	BLACK	TN 1μm,00004MIN.		NICKEL 0.5μm,00002MIN.
LEAD-FREE	GS17F	YELLOW	GOLD 0.1μm,000004MIN.	TN 1μm,00004MIN.	NICKEL 1μm,00004MIN.
LEAD-FREE	GS27F	BROWN	GOLD 0.76μm,00003MIN.		
LEAD-FREE	GS37F	RI UF	GOLD 0.25μm,00001MIN.		

64	78.74 (3.100)	86.34 (3.400)	96.62 (3.804)	100.74 (3.966)	90.52 (3.564)
60	73.66 (2.900)	81.26 (3.200)	91.54 (3.604)	95.66 (3.766)	85.44 (3.364)
50	60.96 (2.400)	68.56 (2.700)	78.84 (3.104)	82.96 (3.266)	72.74 (2.864)
40	48.26 (1.900)	55.86 (2.200)	66.14 (2.604)	70.26 (2.766)	60.04 (2.364)
34	40.64 (1.600)	48.24 (1.900)	58.52 (2.304)	62.64 (2.466)	52.42 (2.064)
30	35.56 (1.400)	43.16 (1.700)	53.44 (2.104)	57.56 (2.266)	47.34 (1.864)
26	30.48 (1.200)	38.08 (1.500)	48.36 (1.904)	52.48 (2.066)	42.26 (1.664)
20	22.86 (900)	30.46 (1.200)	40.74 (1.604)	44.86 (1.766)	34.64 (1.364)
16	17.78 (700)	25.38 (1.000)	35.66 (1.404)	39.78 (1.566)	29.56 (1.164)
14	15.24 (600)	22.84 (900)	33.12 (1.304)	37.24 (1.466)	27.02 (1.064)
10	10.16 (400)	17.76 (700)	28.04 (1.104)	32.16 (1.266)	21.94 (864)
NO. OF	DIM. A	DIM. B	DIM. C	DIM. D	DIM. E

REVISED	EC NO: J2006-0712 DRAWN: AYANAGI MOTTO 2005/10/03 CHKD: M TANAKA 2005/10/06 APPR: NUKITA 2005/10/14	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION		
			10 UNDER	± 0.2	DRAWN BY H. HIRAMOTO	DATE 1989/12/04	TITLE QIK FLECS HEADER ASS'Y R.A. WITH DUAL FUNCTION EJECT LEVERS				
			10 OVER 30 UNDER	± 0.25	CHECKED BY						DATE
			30 OVER	± 0.3	APPROVED BY		DATE		 MOLEX INCORPORATED		
			ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.				SHEET NO.
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE SHEET 2 OF 2		SD-5578-001				1 OF 2
		REV	SIZE A3 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								

