

*World Leader in Network and Electrical Solutions*[HOME](#) | [SOLUTIONS](#) | [RESOURCES](#) | [PRODUCTS](#) | [SERVICES](#) | [LEARNING](#)SEARCH Current refinements (click ☐ to remove)☒ **Region** ▶ **USA** ☒ **Product Family** ▶ **HSTTP PVC Heat Shrink** ☒ **Text Search:** 'HSTTP06-QY'**Your search criteria matched only one product, shown below.****PVC DRY-SHRINK™ Heat Shrink Tubing in Reels**

- For dry locations
 - Flexible, highly flame retardant tubing
 - Good resistance to most fuels and oils
 - Good cut through and solder resistance
 - Material Type: Polyvinyl Chloride Cross-Linked
 - Shrink Ratio: 2:1
 - Temperature Range: -4°F to 221°F (-20°C to 105°C)
 - Voltage: 600V
 - UL VW-1 Recognized, CSA Certified
-
- For dry locations
 - Flexible, highly flame retardant tubing
 - Good resistance to most fuels and oils
 - Good cut through and solder resistance

Part Number:	HSTTP06-QY
RoHS Compliancy Status:	Compliant
Note:	HSTTP06-QY replaces HSTTP06-Q
Part Description:	Flexible, Flame Retardant PVC material offers good cut through and solder resistance.
Material:	Polyvinyl Chloride Cross-Linked
Color:	Black
CSA Certified:	Yes
UL Recognized:	E122770
Length (ft.):	25
Length (m):	7.5
Flammability Rating:	UL224 VW-1
Max. Recovered I.D. (In.):	.031
Max. Recovered I.D. (mm):	.8
Min. Expanded I.D. (In.):	.063
Min. Expanded I.D. (mm):	1.6
Nominal Diameter / Size:	1/16
Nominal Recovered Wall Thickness (In.):	.020
Nominal Recovered Wall Thickness (mm):	.5
Shrink Ratio:	2:1
Temperature Range:	-4°F to 221°F (-20°C to 105°C)
Min. Order UOM:	RL
Min. Order Qty.:	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to My Catalog	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.

[legal information](#) | [privacy policy](#) | [site map](#)

Copyright © 1995-2007, PANDUIT CORP. All rights reserved.