


5X7 Dot Character VFD Module

CU20045SCPb-T31A

- ❑ 4 Lines of 20 Characters 5mm High
- ❑ High Speed Parallel/Serial Interface
- ❑ Operating Temp -10°C to +65°C
- ❑ Single 5V Supply
- ❑ High Brightness Blue Green Display
- ❑ ASCII, Katakana & Extended Character Font
- ❑ 2 User Definable Character RAM

The module includes the Vacuum Fluorescent Display glass, driver and micro-controller ICs with refresh RAM, character generator and interface logic. The high speed 8 bit parallel interface is 5V CMOS compatible suitable for connection to a host CPU bus. The asynchronous serial interface accepts baud rates up to 19,200 with or without parity. Two character font tables can be hardware or software selected. User defined characters and many control commands are available.



ELECTRICAL SPECIFICATION

Parameter	Symbol	Value	Condition
Power Supply Voltage	V _{CC}	5.0VDC +/- 5%	GND=0V
Power Supply Current	I _{CC}	310mA typ.	V _{CC} =5V
Logic High Input	V _{IH}	0.8 V _{CC} min	V _{CC} =5V
Logic Low Input	V _{IL}	0.3 V _{CC} max	V _{CC} =5V
Logic High Output	V _{OH}	V _{CC} -1.5 min.	I _{OH} = -5.0mA
Logic Low Output	V _{OL}	1.5VDC max.	I _{OL} =5.0mA

The power on rise time should be less than 50ms. The inrush current at power on can be 2 x I_{CC}.

OPTICAL and ENVIRONMENTAL SPECIFICATIONS

Parameter	Value
Character Size/Pitch (XxY mm)	3.0 x 5.0/4.6 x 7.0
Dot Size/Pitch (XxY mm)	0.4 x 0.5/0.65 x 0.75
Luminance	700 cd/m ² (204 fL) Typ.
Colour of Illumination	Blue-Green (Filter for colours)
Operating Temperature	-10°C to +65°C
Storage Temperature	-40°C to +85°C
Operating Humidity (non condensing)	20 to 80% RH @ 25°C

SOFTWARE COMMANDS

Instruction	D0-D7	Instruction	D0-D7
Back Space	08H	International Font	18H
Horizontal Tab	09H	Katakana Font	19H
Line Feed	0AH	Euro Currency Mark	1AH
Form Feed	0CH	Escape	1BH
Carriage Return	0DH	> Send User Font	+43H
Clear Display	0EH	> Position cursor	+48H
Clear Line	0FH	> Software Reset	+49H
Increment Write Mode	11H	> Luminance	+4CH
Vertical Scroll Mode	12H	> Flickerless Write	+53H
Horizontal Scroll mode	13H	> Cursor Blink Speed	+54H
5x7 Block Cursor On	15H	Character Data	20H-FFH
Cursor Off	14,16,17H		

TIMING PARAMETERS (min)

Data Set Up To Write	100ns
Write Pulse Width	160ns
Hold After Write	10ns

Subject to change without notice.
Detailed specification on request.
IUK Doc Ref:3521 Iss:1 13Aug01

Dimensions in mm & subject to tolerances. Mounting holes 3.5mm dia.

CHARACTER FONTS

	International Font																Additional Katakana Font													
	00	10	20	30	40	50	60	70	80	90	A0	B0	C0	D0	E0	F0	80	90	A0	B0	C0	D0	E0	F0						
00																														
01																														
02																														
03																														
04																														
05																														
06																														
07																														
08																														
09																														
0A																														
0B																														
0C																														
0D																														
0E																														
0F																														

IDC DATA CONNECTOR

Pin	Sig	Pin	Sig
1	D7	2	D6
3	D5	4	D4
5	D3	6	D2
7	D1	8	D0
9	WR	10	CS
11	SIN/TEST	12	BUSY
13	GND (0V)	14	GND (0V)
15	V _{CC} (5V)	16	V _{CC} (5V)

3 PIN POWER CONNECTOR

Pin	Sig
1	V _{CC} (5V)
2	SIN/TEST
3	GND (0V)

Mates with AMP171822-3

PCB JUMPERS (O)PEN (L)INK

Baud	J2	J1	J0
19200	O	O	O
9600	O	O	L
4800	O	L	O
2400	O	L	L
1200	L	O	O
Parity	J4		J3
EVEN	O		O
ODD	O		L
NONE	L		L / O
Font		JA	
International		1	
JIS		0	

Noritake Sales Office Tel Nos
 Nagoya Japan: +81 (0)52-561-9867
 Canada: +1-416-291-2946
 Chicago USA: +1-847-439-9020
 Munchen (D): +49 (0)89-3214-290
 Itron UK: +44 (0)1493 601144
 Rest Europe: +49 (0)61-0520-9220
 www.noritake-itrn.com