

SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Materials

Item 1 insulating body	Thermoplastic (UL94V-0)
Item 2 Steel screw	Screw, Zinc plating("+/-" slot type)
Item 3 Wire guard	Stainless steel
Item 4 Terminal body	Brass Tin plated

Electrical

- Voltage rating: 300VAC
- Current rating: 8A
- Wire range:
 - Solid wire(AWG): 14-26
 - Stranded wire(AWG): 14-26
- Torque(Lb-In): 2.6
- Screw: M2.5
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -30°C to +105°C
- Soldering temperature: 250°C±10°C/5 Sec

RoHS Compliant


PART NUMBER:

OSTT3XX0453


No. of Poles
 02: 2 Poles
 03: 3 Poles
 ...
 24: 24 Poles

COLOR
 0: Black
 5: Green (Standard)
 6: Blue
 8: Grey

THESE DRAWINGS AND SPECIFICATIONS
 ARE THE PROPERTY OF ON-SHORE
 TECHNOLOGY, INC. AND SHALL NOT BE
 REPRODUCED, COPIED OR USED IN ANY
 MANNER WITHOUT THE PRIOR WRITTEN
 CONSENT OF ON-SHORE TECHNOLOGY,
 INC.



N=Number of poles



P.C.B. LAYOUT

OST ON-SHORE TECHNOLOGY, INC.						
TITLE		OSTT3 5.0 Series 90°				
PART NO.		OSTT3XX0453		DWG NO.	OSTT3XX0453.DWG	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance
		熊海素	熊海素		UNIT: mm	X. ±0.50
		11/08/06	11/08/06		SCALE: NONE	X.X ±0.30
				SHEET: 01/01	REV: B	X.XX ±0.10
						X° ±1°