






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
P		REDRAW BY CAD ECO-14-013531	08SEP2014	NCL	LWP
R		REVISED DRAWING ECO-14-019222	27APR2015	NCL	GOJ
S		REVISED DRAWING ECO-18-014030	11SEP2018	NCL	JMN




SECTION A-A
SCALE 7:1



SECTION B-B
SCALE 7:1



SECTION C-C



PERSPECTIVE VIEW
SCALE 2:1

1 - OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER
D.RENAUD/D.SINISI

1 OBSOLETE
1 OBSOLETE

4,9	PRE-ESTANHADO / PRE TINNED	LATÃO / BRASS	880399-5
4,3	ESTANHADO / TINNED	COBRE FERRO	880399-4
4,3		COBRE FERRO	880399-3
4,2±0,2	PRE-ESTANHADO / PRE TINNED	LATÃO / BRASS	880399-2
4,2±0,2	—	LATÃO / BRASS	880399-1
DIM. "X"	FINISH	MATERIAL	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 08SEP2014 NCLAPRESA CHK 08SEP2014 ECHRISTIANO APVD 08SEP2014 LWPRADO	TE Connectivity TE FUSE CONTACT
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0,5 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±1° FINISH	PRODUCT SPEC - APPLICATION SPEC - WEIGHT -	
MATERIAL SEE TABLE -	SEE TABLE -	Customer Drawing	NAME -
WIRE RANGE >2,5-5,0mm ²		SIZE A2	CAGE CODE 00779
INSUL. RANGE Ø 3,3-5,0mm		DRAWING NO 880399	RESTRICTED TO -
		SCALE 3:1	SHEET 1 OF 1
			REV S