

**Part Number: 75235-4707***Image not available*

Status: Active - Custom
Series: 75235
Category: Backplane Connectors
Overview: GbX® Backplane Connector System

*Series image - Reference only***Mates With Part(s):**
[75220](#) GbX® Daughtercard**Product Environmental Compliance**[EU RoHS](#): RoHS Compliant by Exemption[China RoHS](#): [REACH SVHC](#):[Low-Halogen Status](#): Not Reviewed

Part Detail**General**

Status	Active - Custom
Category	Backplane Connectors
Series	75235
Application	Backplane
Application Tooling Documents	TM-622022099
Comments	Right Guide Header, No Keying Postion
Component Type	PCB Header
Overview	GbX® Backplane Connector System
Product Name	GbX®
Style	N/A

Physical

Circuits (Loaded)	56
Circuits (maximum)	56
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	Yes
Keying to Mating Part	None
Material - Plating Mating	Gold
Number of Columns	7
Number of Pairs	4
Number of Rows	8
Orientation	Vertical
PC Tail Length	2.20mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	1.85mm
Pitch - Termination Interface	1.85mm
Polarized to PCB	No
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	105°C

Electrical**(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	1A
Data Rate	8.0 Gbps
Real Signals (per 25mm)	108
Shield Type	Ground Plane Shield
Shielded	Yes
Voltage - Maximum	120V AC (RMS)/DC

Agency Certification

UL	E29179
----	--------

Material Info

UPC	822350174862
-----	--------------

Reference - Drawing Numbers

Product Specification	PS-75221-999
Sales Drawing	SD-75235-470

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Insertion Tool for 4-Pair by 7-Column	0622022120

Previously Available Application**Tooling**

[Check our list of old tooling that used to be available for this part](#)