




LOC	DIST	REVISIONS				
		REV	LTR	DESCRIPTION	DATE	DWN APVD
AJ	16	J		REV PER ECO 08-009474	7/21/2008	DW JL



RECOMMENDED PANEL CUTOUT



PCB CONFIGURATION

- 1 POLYESTER PBT PER MIL-M-24519, TYPE GPT-15F, UL94V-O RATED, COLOR:NATURAL
- 2 POLYESTER PBT PER MIL-M-24519, TYPE GPT-15F, UL94V-O RATED, COLOR:BLACK
- 3 POLYMETHYLPENTENE, GENERAL PURPOSE.
- 4 ZINC PER QQ-Z-363.
- 5 BERYLLIUM COPPER PER QQ-C-530.
- 6 BRASS PER ASTM-B-453.
- 7 NICKEL PLATE PER QQ-N-290
3.81 μm [.000150] MINIMUM THICK.
- 8 TIN PLATE PER ASTM-B-545
3.81 μm [.000150] MINIMUM THICK.
- 9 GOLD PLATE PER MIL-G-45204
0.76 μm [.000030] MINIMUM THICK.
10. SEE INSTRUCTION SHEET 2769.

	413194-2
	413194-1
HOUSING MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. SCOTT CHK J. LIPPERT	11-29-90 2-1-91	Tyco Electronics Corporation Middletown, PA 17057	
DIMENSIONS: INCHES		PRODUCT SPEC	NAME	JACK, RIGHT ANGLE, PCB, 75 OHM, BNC	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO
0. PLC ± -		—	A1	00779	413194
1. PLC ± -		—	RESTRICTED TO		—
2. PLC ± 0.06 [.002]		—	CUSTOMER DRAWING		SCALE 4:1
3. PLC ± -		—	SHEET 1 OF 1		REV J
4. PLC ± -		—	REV		—
ANGLES ± -		—			
FINISH SEE NOTES 7-9		WEIGHT —			
MATERIAL SEE NOTES 1-6		—			