

SEV SERIES

85°C Standard, Lead Free Reflow Soldering.

◆ FEATURES

- Case Dia $\phi 3 \sim \phi 18\text{mm}$
- Lead free reflow soldering is available.
- Available for high density mounting.
- RoHS compliance.



◆ SPECIFICATIONS



Items	Characteristics																																																											
Category Temperature Range	-40 ~ +85℃																																																											
Rated Voltage Range	4~100V.DC																																																											
Capacitance Tolerance	± 20%(20℃,120Hz)																																																											
Leakage Current(MAX)	I=0.01CV or 3 μ A whichever is greater. (After 2 minutes application of rated voltage) I=Leakage Current(μA) C=Rated Capacitance(μF) V=Rated Voltage(V)																																																											
Dissipation Factor(MAX) (tanδ)	<table><tr><th>Rated Voltage (V)</th><th>4</th><th>6.3</th><th>10</th><th>16</th><th>25</th><th>35</th><th>50</th><th>63</th><th>100</th></tr><tr><td>φ 3</td><td>0.40</td><td>0.30</td><td>—</td><td>0.20</td><td>0.16</td><td>0.14</td><td>0.14</td><td>—</td><td>—</td></tr><tr><td>φ 4, φ 5, φ 6.3×5.5</td><td>0.40</td><td>0.26</td><td>0.22</td><td>0.18</td><td>0.16</td><td>0.13</td><td>0.12</td><td>—</td><td>—</td></tr><tr><td>φ 6.3×8, φ 8~φ 12.5</td><td>0.50</td><td>0.35</td><td>0.26</td><td>0.20</td><td>0.16</td><td>0.14</td><td>0.12</td><td>0.12</td><td>0.10</td></tr><tr><td>φ 16, φ 18</td><td>—</td><td>0.48</td><td>0.34</td><td>0.24</td><td>0.18</td><td>0.14</td><td>0.12</td><td>0.12</td><td>0.10</td></tr></table> When rated capacitance is over 1000μF, tanδ shall be added 0.02 to the listed value with increase of every 1000μF.										Rated Voltage (V)	4	6.3	10	16	25	35	50	63	100	φ 3	0.40	0.30	—	0.20	0.16	0.14	0.14	—	—	φ 4, φ 5, φ 6.3×5.5	0.40	0.26	0.22	0.18	0.16	0.13	0.12	—	—	φ 6.3×8, φ 8~φ 12.5	0.50	0.35	0.26	0.20	0.16	0.14	0.12	0.12	0.10	φ 16, φ 18	—	0.48	0.34	0.24	0.18	0.14	0.12	0.12	0.10
Rated Voltage (V)	4	6.3	10	16	25	35	50	63	100																																																			
φ 3	0.40	0.30	—	0.20	0.16	0.14	0.14	—	—																																																			
φ 4, φ 5, φ 6.3×5.5	0.40	0.26	0.22	0.18	0.16	0.13	0.12	—	—																																																			
φ 6.3×8, φ 8~φ 12.5	0.50	0.35	0.26	0.20	0.16	0.14	0.12	0.12	0.10																																																			
φ 16, φ 18	—	0.48	0.34	0.24	0.18	0.14	0.12	0.12	0.10																																																			
Endurance	<table><tr><td>Capacitance Change</td><td colspan="10">Within ±25% of the initial value.</td></tr><tr><td>Dissipation Factor</td><td colspan="10">Not more than 200% of the specified value.</td></tr><tr><td>Leakage Current</td><td colspan="10">Not more than the specified value.</td></tr></table>										Capacitance Change	Within ±25% of the initial value.										Dissipation Factor	Not more than 200% of the specified value.										Leakage Current	Not more than the specified value.																										
Capacitance Change	Within ±25% of the initial value.																																																											
Dissipation Factor	Not more than 200% of the specified value.																																																											
Leakage Current	Not more than the specified value.																																																											
Low Temperature Stability Impedance Ratio(MAX)	<table><tr><th>Rated Voltage (V)</th><th>4</th><th>6.3</th><th>10</th><th>16</th><th>25</th><th>35</th><th>50</th><th>63</th><th>100</th></tr><tr><td>Z(-25℃)/Z(20℃)</td><td>7</td><td>4</td><td>3</td><td>2</td><td>2</td><td>2</td><td>2</td><td>2</td><td>2</td></tr><tr><td>Z(-40℃)/Z(20℃)</td><td>15</td><td>8</td><td>8</td><td>4</td><td>4</td><td>3</td><td>3</td><td>5</td><td>5</td></tr></table> (120Hz)										Rated Voltage (V)	4	6.3	10	16	25	35	50	63	100	Z(-25℃)/Z(20℃)	7	4	3	2	2	2	2	2	2	Z(-40℃)/Z(20℃)	15	8	8	4	4	3	3	5	5																				
Rated Voltage (V)	4	6.3	10	16	25	35	50	63	100																																																			
Z(-25℃)/Z(20℃)	7	4	3	2	2	2	2	2	2																																																			
Z(-40℃)/Z(20℃)	15	8	8	4	4	3	3	5	5																																																			

◆ MULTIPLIER FOR RIPPLE CURRENT

Frequency coefficient

Frequency (Hz)		60(50)	120	500	1k	10k≤
Coefficient	0.1~1μF	0.50	1.00	1.20	1.30	1.50
	2.2~4.7μF	0.65	1.00	1.20	1.30	1.50
	10~47μF	0.80	1.00	1.20	1.30	1.50
	100~1000μF	0.80	1.00	1.10	1.15	1.20
	2200~10000μF	0.80	1.00	1.05	1.10	1.15

MARKING




Voltage code								
(V) Rated Voltage	6.3	10	16	25	35	50	63	100
Rated Voltage code	0J	1A	1C	1E	1V	1H	1J	2A

◆ PART NUMBER

□□□ Rated Voltage	SEV Series	□□□□□ Rated Capacitance	□ Capacitance Tolerance	□□□ Option	DxL Case Size
---	----------------------------------	---	---	----------------------------------	-------------------------------------

◆ DIMENSIONS

(mm)



Vibration proof package are available for ϕ 8 to ϕ 18.
For details, please consult us.

ϕ	D	L	A ₁	B ₁	C	W ₁	P	K	α
3	5.5	3.3	3.3	1.5	0.45~0.8	0.8	0.5 MAX	0	
4	5.5	4.3	4.3	1.8	0.5~0.8	1.0	0.5 MAX	0	
5	5.5	5.3	5.3	2.2	0.5~0.8	1.3	0.5 MAX	0	
6.3	5.5	6.6	6.6	2.7	0.5~0.8	1.8	0.5 MAX	0	
6.3	8	6.6	6.6	2.7	0.5~0.8	1.8	0.5 MAX	0	
8	6.5	8.3	8.3	3.4	0.5~0.8	2.2	0.5 MAX	0	
8	10.5	8.3	8.3	2.9	0.8~1.1	3.1	0.5 MAX	0	
10	10.5	10.3	10.3	3.2	0.8~1.1	4.5	0.5 MAX	0	
12.5	13.5	13	13	4.9	0.8~1.1	4.5	0.7±0.4	0.5	
12.5	16	13	13	4.9	0.8~1.1	4.5	0.7±0.4	0.5	
16	16.5	17	17	6	1.0~1.6	6.8	0.7±0.4	0.5	
16	21.5	17	17	6	1.0~1.6	6.8	0.7±0.4	0.5	
18	16.5	19	19	7	1.0~1.6	6.8	0.7±0.4	0.5	
18	21.5	19	19	7	1.0~1.6	6.8	0.7±0.4	0.5	

◆ **STANDARD SIZE**

Size ϕ D×L(mm), Ripple Current (mA r.m.s./85°C, 120Hz)[illegible]