





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	0		G	REVISED PER ECR-13-008204	10DEC2013	KH	TM



SECTION B-B
SCALE 10:1



SECTION A-A
SCALE 10:1

1 0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN-LEAD IN THE TIN-LEAD PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.


2 WIRE RANGE: 0.5-2mm² [20-14] AWG. INSULATION RANGE: 3.30-5.08[.130-.200] DIA.

3 DIMENSIONS IN BRACKETS ARE IN INCHES.

4 0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN IN TIN PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.

5 SUPERSEDED BY 1-770255-0

5	GOLD 4	0.30 [.012]	BRASS	1-770255-0
	GOLD 1	0.30 [.012]	BRASS	770255-2
	PRE-TIN	0.30 [.012]	BRASS	770255-1
	FINISH	MATERIAL		PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. SALMON 23DEC92	 TE Connectivity										
		CHK R. SWING 23DEC92											
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME PIN, GROUNDING, LOOSE PIECE, UNIVERSAL MATE-N-LOK(TM) II —									
		APVD M. TRULL 01APR93											
		PRODUCT SPEC —											
		APPLICATION SPEC —		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO					
MATERIAL		FINISH		WEIGHT		A2 00779		C-770255	—				
SEE TABLE		SEE TABLE		CUSTOMER DRAWING				SCALE	4:1	SHEET	1 of 1	REV	G