




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION		DATE	APVD
FT	0		C	REVISED PER ECO-07-005875		3/23/07	SS

NOTES:


MATERIAL:
HOUSING: THERMOPLASTIC, UL94V-0, BLACK.
TERMINALS: BRIGHT TIN PLATED COPPER ALLOY.
SCREW: 6-32, STEEL, ZINC PLATING W/ CLEAR CHROMATE COATING.

ELECTRICAL:
MAX CURRENT: 20A.
OPERATING VOLTAGE: 300V.
WIRE RANGE: 12-22 AWG


ENVIRONMENTAL PROPERTIES:
OPERATING TEMP: 105°C




- 1 CIRCUIT ID MARKED IN WHITE INK.
- 2 NO SCREW IN POSITION 4.
- 3 PRELIMINARY PART NUMBER.




796595-4



796595-1



796595-2



796595-3


SEE FIGURE 3

SEE FIGURE

SEE FIGURE 1

SEE FIGURE 1

7.561	20	BC6-P108-20	7-1437662-9
7.186	19	BC6-P108-19	6-1437662-7
6.811	18	BC6-P108-18	7-1437662-8
6.436	17	BC6-P108-17	7-1437662-7
6.061	16	BC6-P108-16-291	796595-4
6.061	16	BC6-P108-16	1-1437662-9
5.686	15	BC6-P108-15	7-1437662-6
5.311	14	BC6-P108-14	1-1437662-8
4.936	13	BC6-P108-13	7-1437662-5
4.561	12	BC6-P108-12	1-1437662-7
4.186	11	BC6-P108-11	1-1437662-6
3.811	10	BC6-P108-10	1-1437662-5
3.436	9	BC6-P108-09	1-1437662-3
3.061	8	BC6-P108-08	1-1437662-2
2.686	7	BC6-P108-07	1-1437662-1
2.311	6	BC6-P108-06-284	796595-1
2.311	6	BC6-P108-06	1-1437662-0
1.936	5	BC6-P108-05	1437662-9
1.561	4	BC6-P108-04	1437662-8
1.186	3	BC6-P108-03-290	796595-3
1.186	3	BC6-P108-03-289	796595-2
1.186	3	BC6-P108-03	1437662-5
.811	2	BC6-P108-02	1437662-4
DIM. A REF.	NO. OF POS.	CATALOG NUMBER	TYCO PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. SCHLEGEL 8/25/04	tyco Tyco Electronics Corporation				
		CHK S. YODER 8/25/04	Harrisburg, Pa 17105-3608				
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD S. YODER 8/25/04	NAME BC6-P108-XX ASSEMBLY				
	0 PLC ± -	PRODUCT SPEC	-				
	1 PLC ± -	—	-				
	2 PLC ± .02	APPLICATION SPEC	-				
	3 PLC ± .010	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
MATERIAL	FINISH	WEIGHT	A3 00779 C-1437662-1			—	
—	—	CUSTOMER DRAWING			SCALE NTS	SHEET 1 OF 1	REV C