



LED Display

Product Data Sheet

LTP-2258CA

Spec No.: DS-30-99-496

Effective Date: 06/06/2000

Revision: -

LITE-ON DCC

RELEASE

BNS-OD-FC001/A4

LITE-ON Technology Corp. / Optoelectronics

No.90,Chien 1 Road, Chung Ho, New Taipei City 23585, Taiwan, R.O.C.

Tel: 886-2-2222-6181 Fax: 886-2-2221-1948 / 886-2-2221-0660

<http://www.liteon.com/opto>

FEATURES

- * 1.95 INCH (49.45 mm) MATRIX HEIGHT
- * LOW POWER REQUIREMENT
- * SINGLE PLANE, WIDE VIEWING ANGLE
- * 5×8 ARRAY WITH X-Y SELECT
- * COMPATIBLE WITH ASCII AND EBCDIC CODES
- * STACKABLE VERTICALLY AND HORIZONTALLY
- * EASY MOUNTING ON P.C. BOARD
- * BINNED FOR LUMINOUS INTENSITY AND DOMINANT WAVELENGTH


DESCRIPTION

The LTP-2258CA is a 1.95 inch (49.45 mm) matrix height 5×8 dot matrix displays. This device utilizes Red Orange and green LED chips. The Red Orange LED chips are made from GaAsP on GaP substrate, the green LED chips are made from GaP on GaP substrate, and this display has gray face and white dots.

DEVICE


PART NO.	DESCRIPTION
MULTI-COLOR	ANODE COLUMN
LTP-2258CA	CATHODE ROW

PACKAGE DIMENSIONS



NOTES: All dimensions are in millimeters. Tolerances are ± 0.25 mm (0.01") unless otherwise noted.

INTERNAL CIRCUIT DIAGRAM



PIN CONNECTION

No.	CONNECTION	No.	CONNECTION
1	CATHODE ROW 6 GREEN	12	CATHODE ROW 3 GREEN
2	CATHODE ROW 6 RED ORANGE	13	CATHODE ROW 3 RED ORANGE
3	CATHODE ROW 8 GREEN	14	CATHODE ROW 1 GREEN
4	CATHODE ROW 8 RED ORANGE	15	CATHODE ROW 1 RED ORANGE
5	ANODE COLUMN 2	16	ANODE COLUMN 4
6	ANODE COLUMN 3	17	ANODE COLUMN 3
7	CATHODE ROW 5 GREEN	18	CATHODE ROW 4 GREEN
8	CATHODE ROW 5 RED ORANGE	19	CATHODE ROW 4 RED ORANGE
9	ANODE COLUMN 5	20	ANODE COLUMN 1
10	CATHODE ROW 7 GREEN	21	CATHODE ROW 2 GREEN
11	CATHODE ROW 7 RED ORANGE	22	CATHODE ROW 2 RED ORANGE

ABSOLUTE MAXIMUM RATING AT Ta=25°C

PARAMETER	GREEN	UNIT
Average Power Dissipation Per Dot	36	mW
Peak Forward Current Per Dot	100	mA
Average Forward Current Per Dot	13	mA
Derating Linear From 25°C Per Dot	0.17	mA/°C
Reverse Voltage Per Dot	5	V
Operating Temperature Range	-35°C to +85°C	
Storage Temperature Range	-35°C to +85°C	
Solder Temperature: max 260°C for max 3sec at 1.6mm[1/16inch] below seating plane.		

ELECTRICAL / OPTICAL CHARACTERISTICS AT Ta=25°C**GREEN**

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
Average Luminous Intensity	I _v	1780	4800		μcd	I _p =80mA 1/16Duty
Peak Emission Wavelength	λ _p		565		nm	I _F =20mA
Spectral Line Half-Width	Δλ		30		nm	I _F =20mA
Dominant Wavelength	λ _d		569		nm	I _F =20mA
Forward Voltage any Dot	V _F		2.1	2.6	V	I _F =20mA
			3.0	3.7		I _F =80mA
Reverse Current any Dot	I _R			100	μA	V _R =5V
Luminous Intensity Matching Ratio	I _v -m			2:1		I _F =10mA

Note: Luminous intensity is measured with a light sensor and filter combination that approximates the CIE (Commision Internationale De L'Eclairage) eye-response curve.

ABSOLUTE MAXIMUM RATING AT Ta=25°C

PARAMETER	RED ORANGE	UNIT
Average Power Dissipation Per Dot	36	mW
Peak Forward Current Per Dot	100	mA
Average Forward Current Per Dot	13	mA
Derating Linear From 25°C Per Dot	0.17	mA/°C
Reverse Voltage Per Dot	5	V
Operating Temperature Range	-35°C to +85°C	
Storage Temperature Range	-35°C to +85°C	
Solder Temperature: max 260°C for max 3sec at 1.6mm[1/16inch] below seating plane.		

ELECTRICAL / OPTICAL CHARACTERISTICS AT Ta=25°C
RED ORANGE

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
Average Luminous Intensity	I _v	1780	4800		μcd	I _p =80mA 1/16Duty
Peak Emission Wavelength	λ _p		630		nm	I _F =20mA
Spectral Line Half-Width	Δλ		40		nm	I _F =20mA
Dominant Wavelength	λ _d		621		nm	I _F =20mA
Forward Voltage any Dot	V _F		2.0	2.6	V	I _F =20mA
			2.6	3.4		I _F =80mA
Reverse Current any Dot	I _R			100	μA	V _R =5V
Luminous Intensity Matching Ratio	I _v -m			2:1		I _F =10mA

Note: Luminous intensity is measured with a light sensor and filter combination that approximates the CIE (Commision Internationale De L'Eclairage) eye-response curve.

TYPICAL ELECTRICAL / OPTICAL CHARACTERISTIC CURVES

(25°C Ambient Temperature Unless Otherwise Noted)




Fig1. RELATIVE INTENSITY VS. WAVELENGTH




Fig2. RELATIVE LUMINOUS EFFICIENCY (LUMINOUS INTENSITY PER UNIT CURRENT) VS. PEAK CURRENT (REFRESH RATE 1KHz)




Fig3. FORWARD CURRENT VS. FORWARD VOLTAGE




Fig4. RELATIVE LUMINOUS INTENSITY VS. FORWARD CURRENT




Fig5. MAX. AVERAGE FORWARD CURRENT VS. AMBIENT TEMPERATURE.




Fig6. MAX. PEAK CURRENT VS. DUTY CYCLE % (REFRESH RATE 1KHz)

NOTE: G=GREEN E= RED ORANGE