


2330QD, 2332QD and 2390QD Series Non-Relampable Neon-Incandescent Indicator Lights

Description and Features



Mounting: Will snap-fit into Ø.032/.100 thick panels, use speednut for other panel thicknesses.

Mounting hole pattern on page SP3.

Terminals: Quick-connect, tinned brass .187 x .020

Lens: Polycarbonate

Bezel: Polished stainless steel.

Lens Color	Neon	Incandescent
	Model No. (105-125VAC) .250 Terminals	Model No. (28V) .250 Terminals
Red	2330QD1	2390QD1-28V
Amber	2330QD3	2390QD3-28V
White	2330QD4	2390QD4-28V
Green	2332QD5*	2390QD5-28V
Lamp used	C6A+Resistor	#2187

*Incorporates G2B lamp and resistor
Underwriters Laboratories (UL) File No. E20356

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

VCC:

[2330QD1](#) [2330QD3](#) [2330QD4](#) [2332QD5](#) [2390QD1-28V](#) [2390QD4-28V](#) [2390QD3-28V](#) [2390QD5-28V](#)