








CATALOG LISTING
4TL247-550 SERIES
PAGE 1 OF 1
CHART 1
REPLACES
RELEASE NO. PR-14717
CHECK
30 JULY 99
J A F
CHECK
30 JULY 99
J A F
CHECK
30 JULY 99
J A F
FORMTEK
DRAWN
J J A
30 JULY 99
CHECK
30 JULY 99
J A F
CHECK
30 JULY 99
J A F



	CATALOG LISTING △ 6	AVAILABLE LOCKING COMBINATIONS FOR CONFIGURATION SEE LETTERING DETAILS		CURRENT CAPACITY (AMPS)											
				RESISTIVE LOAD DC VOLTS			AC VOLTS		LAMP LOAD		INDUCTIVE LOAD				
				28	125	250	125	250	28 VDC	125 VAC	28 VDC	125 VAC			
				18	.75	.5	11	6	4	2	10	8			
4TL247-550		B, E, G, L, N, P													
"A" △ 3  LOCKED IN THREE POSITIONS	"B" △ 3  LOCKED IN CENTER AND EXTREME POSITION (KEYWAY SIDE)	"D" △ 3  LOCKED OUT OF CENTER POSITION	"E" △ 3  LOCKED IN CENTER POSITION	"F" △ 3  LOCKED IN EXTREME POSITION (OPPOSITE KEYWAY)	 LOCKWASHER △ 4  LOCKING RING △ 4  HEX NUT (2) △ 4										
"G" △ 3  LOCKED IN EXTREME POSITION (KEYWAY SIDE)	"H" △ 3  LOCKED OUT OF CENTER AND EXTREME POSITION (KEYWAY SIDE)	"J" △ 3  LOCKED OUT OF CENTER AND EXTREME POSITION (OPPOSITE KEYWAY)	"K" △ 3  LOCKED IN CENTER AND EXTREME POSITION (OPPOSITE KEYWAY)	"L" △ 3  LOCKED OUT OF EXTREME POSITION (KEYWAY SIDE)											
"M" △ 3  LOCKED OUT OF AND INTO EXTREME POSITION (OPPOSITE KEYWAY)	"N" △ 3  LOCKED OUT OF EXTREME POSITION (OPPOSITE KEYWAY)	"P" △ 3  LOCKED OUT OF AND INTO EXTREME POSITION (KEYWAY SIDE)													
CIRCUIT MADE WITH TOGGLE LEVER IN															
KEYWAY SIDE		CENTER		OPPOSITE KEYWAY											
															
MAINTAINED POSITION		MAINTAINED POSITION		MOMENTARY POSITION											

- NOTES
- 1 - SWITCHES ARE CAPABLE OF WITHSTANDING A TEMPERATURE OF 160°F CONTINUOUSLY AT FULL RATED LOAD
 - 2 - CIRCUIT DESIGNATION AND MICRO SWITCH CATALOG LISTING MARKED ON SIDE OF SWITCH
 - △ 3 KEYWAY SHOWN ON LEFT SIDE
 - △ 4 FURNISHED UNASSEMBLED
 - 5 - FOR TERMINAL COVER SEE MICRO SWITCH CATALOG LISTING 5PA9
 - △ 6 SUFFIX LETTER MUST BE ADDED FOR DESIRED TYPE TOGGLE LOCKING. SEE CHART FOR AVAILABLE LOCKING COMBINATIONS
 - △ 7 FROM BOTTOM OF KEYWAY TO MAJOR DIAMETER OF 15/32 THREAD

L192 10A 125, 250, 277 VAC
1/4HP 125 VAC,
1/2HP 250, 277 VAC
3A 125 VAC "L"



THIRD ANGLE PROJECTION			
SCALE FULL			
DO NOT SCALE PRINT			
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE			
ONE PLACE	(.0)	±.030	
TWO PLACE	(.00)	±.015	
THREE PLACE	(.000)	±.005	
ANGLES		±	
WEIGHT			