

# Small Form Factor

## Multimode 850 nm 2X5 Fiber Optic Transceiver

### 1.25Gbit/sec Gigabit Ethernet

#### FEATURES

- 1.25Gbps Gigabit Ethernet Performance
- Compliant with IEEE802.3 Gigabit Ethernet standard
- Small Form Factor transceiver
- RJ-45 style LC™ connector system
- 850 nm Vertical Cavity Surface Emitting Laser (VCSEL) Source Technology
- Data Link up to 500 Meters min in 50/125um MMF and 300 Meters min in 62.5/125um MMF
- Single + 3.3V Power Supply and PECL Logic Interface IO (DC Coupled)
- PECL Signal detection output
- Class 1 FDA and IEC laser safety compliant (Laser Class 1 Product)

#### Absolute Maximum Ratings

Parameter	Symbol	Min.	Typ.	Max.	Unit	Reference
Storage temperature	T <sub>s</sub>	-40		85	°C	
Lead soldering temperature	T <sub>SOLD</sub>			260	°C	
Lead soldering time	t <sub>SOLD</sub>			10	sec.	
Supply voltage	V <sub>cc</sub>	0		6	V	

#### Recommended Operating Conditions:

Parameter	Symbol	Min.	Typ.	Max.	Unit	Reference
Ambient Operating Temperature	T <sub>A</sub>	0		70	°C	
Supply voltage	V <sub>cc</sub>	3.1		3.5	V	
Transmitter Differential Input Voltage	V <sub>D</sub>	0.3		1.6	V	
Data Output Load	R <sub>DL</sub>		50		Ω	

 <b>DELTA</b> DELTA ELECTRONICS, INC.	TITLE				DATE:	
	LC-1250A2F1				2002/03/25	
WRITTEN	CHECKED	APPROVED	DOCUMENT NO:		REV:	
			Alston H.	Teddy Kuo		YY Tsai

# Small Form Factor

## Multimode 850 nm 2X5 Fiber Optic Transceiver

### 1.25Gbit/sec Gigabit Ethernet

Transmitter Electro-Optical Performance Specifications:

Parameter	Symbol	Min.	Typ.	Max.	Unit	Reference
Supply current	I <sub>cc</sub>			140	mA	
Launched power(avg.)	P <sub>O</sub>	-9.5		-4	dBm	
Optical extinction ratio		9			dB	
Center wavelength	λ <sub>c</sub>	830	850	860	nm	
Spectral width(RMS)	σ			0.85	nm rms	
Optical risetime	t <sub>r</sub>			0.26	ns	Note(1)
Optical falltime	t <sub>f</sub>			0.26	ns	Note(1)
Relative Intensity Noise	RIN			-117	DB/Hz	

Note(1).These are unfiltered 20-80% values.

Receiver Electro-Optical Performance Specifications:

Parameter	Symbol	Min.	Typ.	Max.	Unit	Reference
Supply current	I <sub>cc</sub>			130	mA	
Data output differential voltage	V <sub>D</sub>	0.5	0.7	1.23	V	
Optical input sensitivity(avg.)	P <sub>IN</sub>			-17	dBm	Note(1)
Optical input saturation(avg.)	P <sub>SAT</sub>	-3			dBm	Note(1)
Optical wavelength	λ		850		nm	
Signal detect-Assert	P <sub>A</sub>			-17	dBm	
Signal detect-Deassert	P <sub>D</sub>	-30			dBm	
Signal detect-Hysteresis	P <sub>A</sub> - P <sub>D</sub>	0.5			dB	

Note(1).With BER better than or equal to  $1 \times 10^{-12}$ ,measured in the center of the eye opening with 2<sup>7</sup>-1 NRZ PRBS

 <b>DELTA</b> DELTA ELECTRONICS, INC.	TITLE				DATE:
	LC-1250A2F1				2002/03/25
WRITTEN	CHECKED	APPROVED	DOCUMENT NO:		REV:
Alston H.	Teddy Kuo	YY Tsai	LC-1250A2F1		S3


# Small Form Factor

## Multimode 850 nm 2X5 Fiber Optic Transceiver

### 1.25Gbit/sec Gigabit Ethernet

Recommended Circuit Schematic

Small Form Factor Multimode 850nm Gigabit Ethernet 2x5 Transceiver, 3.3V Transceiver Version



\* Disable Pin truth table

$$C_{1/2/3} = 4.7 \text{ uF}$$

$$C_{4/5/6/7} = 10 \text{ nF}$$

$$L_{1/2} = 1 \text{ uH}$$

$$R_{1/2} = 82 \Omega$$

$$R_{3/4} = 130 \Omega$$

$$R_{7/8} = 150 \Omega$$

R5/6/9/10/11/12 Depend on SerDes chip used .

R13 = 270 Ω (For PECL output).

R13 = Open (For TTL output).

Input Level (LV-TTL)	TX Function
Low	ON
High	OFF
NIC	ON

Values of R5/6/9/10/11/12 may vary as long as proper  $50 \Omega$  termination to VEE or  $100 \Omega$  differential is provided. For good EMI performance, the power supply filter is required. Use short tracks from the inductor L1/L2 to the module VccTx/VccRx.

 <b>DELTA</b> DELTA ELECTRONICS, INC.	TITLE				DATE: 2002/03/25
	WRITTEN	CHECKED	APPROVED	DOCUMENT NO:	
	Alston H.	Teddy Kuo	YY Tsai	LC-1250A2F1	REV: S3


# Small Form Factor

## Multimode 850 nm 2X5 Fiber Optic Transceiver

### 1.25Gbit/sec Gigabit Ethernet

#### Mechanical Dimensions

Unit : mm



 <b>DELTA</b> DELTA ELECTRONICS, INC.	TITLE				DATE:
	LC-1250A2F1				2002/03/25
	WRITTEN	CHECKED	APPROVED	DOCUMENT NO:	REV:
	Alston H.	Teddy Kuo	YY Tsai	LC-1250A2F1	S3

# Small Form Factor

## Multimode 850 nm 2X5 Fiber Optic Transceiver

### 1.25Gbit/sec Gigabit Ethernet

#### Pin Assignments

Pin	FUNCTION	LOGIC FAMILY
1	RX GOUND	0 V <sub>dc</sub>
2	RX VCC	3.3 V <sub>dc</sub>
3	SD(RX SIGNLE DETECT)	LV-PECL
4	RX-	LV-PECL
5	RX+	LV-PECL
6	TX VCC	3.3 V <sub>dc</sub>
7	TX GND	0 V <sub>dc</sub>
8	TX DISABLE	Note (1)
9	TX+	LV-PECL
10	TX-	LV-PECL

•NOTE (1):

Input Level (LV-TTL)	TX Function
Low	ON
High	OFF
NIC	ON

 <b>DELTA</b> DELTA ELECTRONICS, INC.	TITLE				DATE:	
	LC-1250A2F1				2002/03/25	
	WRITTEN	CHECKED	APPROVED	DOCUMENT NO:		REV:
	Alston H.	Teddy Kuo	YY Tsai	LC-1250A2F1		S3

# Small Form Factor

## Multimode 850 nm 2X5 Fiber Optic Transceiver

### 1.25Gbit/sec Gigabit Ethernet

#### Regulatory Compliance

Test Item	Reference	Qty'	Evaluation
(#1) Electromagnetic Interference EMC	FCC Class B EN 55022 Class B CISPR 22	5	
(#2) Immunity : Radio Frequency Electromagnetic Field	EN 61000-4-3 IEC 1000-4-3	5	
(#3) Immunity : Electrostatic Discharge to the Duplex SC Receptacle	EN 61000-4-2 IEC 1000-4-2 IEC 801.2	5	(1) Satisfied with electrical characteristics of product spec. (2) No physical damage
(#4) Electrostatic Discharge to the Electrical Pins	MIL-STD-883C Method 3015.4  EIAJ#1988.3.2B Version 2, Machine model	5	

 <b>DELTA</b> DELTA ELECTRONICS, INC.	TITLE				DATE:	
	LC-1250A2F1				2002/03/25	
WRITTEN	CHECKED	APPROVED	DOCUMENT NO:		REV:	
Alston H.	Teddy Kuo	YY Tsai	LC-1250A2F1		S3	