



DKB-0325



Die profile



Crimp profile

DKB-0325 is a precision, ratchet crimp tool designed to provide consistent and reliable crimp connections on Uninsulated / Copper tube on wires ranging from .

Easy to use

Open the tool. Insert terminal in correct nest. Close tool until terminal fastened. Insert wire into terminal. Close tool until ratchet release. Attention: To release ratchet mechanism, push the trigger.

Calibration

To calibrate this tool the pre-load has to be measured. Gauge is required to ensure that the die is according to specification. For more information; See instruction sheet.

- Compact, pocketable design.
- Ergonomic handles for low effort crimping.
- Ratchet action to ensure full crimp cycle with safety release.
- Durable - minimum of 50,000 cycles.
- Tool is factory set with a precise eccentric cam adjustment function to guarantee performance.

Technical data

Prod.code:	DKB-0325
Length:	198 mm / 7,80"
Height:	65 mm / 2,56"
Weight:	350 gr / 0,77 lbs
Connector:	Uninsulated / Copper tube
Description:	Indent crimp
Wire size:	22-14 AWG

Distributors address info

--