



ISO9001:2008 Certified

Mechanical Specifications (mm)

D:	9.0	± max
T:	4.3	± max
Lead Diameter	0.5	± nom
S:	5.0	± nom
L:	38.0	± nom
Coating Lead Run Down (straight Leads)	3.0	± max
B:	4.00	± nom
C:	2.20	± nom



Electrical Specifications

Resistance:	20.0 Ω	± 25 %
Max Steady State Current upto 65°C:	2.00	A
Max Rec. Energy Rating:	8	J
Actual Failure Instantaneous Energy:	16	J
Maximum Capacitance @ 120 VAC:	550	μ f
Maximum Capacitance @ 240 VAC:	138	μ f
Resistance @ 100% Max Current:	0.49	Ω
Resistance @ 50% Max Current:	0.96	Ω
Body Temperature at 100% Max Current:	147.00	°C
Dissipation Constant:	9.0	mw/°C
Thermal Time Constant:	20	Sec.
Material Type (for Beta and Curve):	C	

SL08 20002

Date: 02/05/2009	Drawn by: Erin Landis
Ametherm, Inc. 3111 N. Deer Run Road Carson City, Nevada USA 89701 www.ametherm.com	Approved By: Mehdi Samii
	Revision: a