





Rev	AWO #	Description	Date	Appr
-		RELEASED	4/8/05	

APPROVED: _____
DATE: _____ TITLE: _____



PCB LAYOUT



SPECIFICATIONS:

Material: Nylon 66, rated UL 94V-2
Insulator color: White
Contacts: Brass
Plating: Tin over Copper underplate overall
Electrical:
Operating voltage: 250 VAC max
Current rating: 2 Amps max
Contact resistance: 20 mohms max
Insulation resistance: 1,000 Mohms min
Dielectric withstanding voltage: 1,500 VAC for 1 minute
Temperature Rating:
Operating temperature: -25°C to +85°C
Environmental:
Lead free, RoHS compliant
Recommended soldering temp: 260°C for 5 seconds

Positions: 2 thru 20
A = .100 [2.54] x No. of Positions
B = .100 [2.54] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
INCHES				TITLE .100 [2.54] LOCKING HEADER STRAIGHT, PCB			
.X ± .10				Holes			
.XX ± .020				ØXX ± .015			
.XXX ± .015				ØXXX ± .010			
APPROVALS				DATE			
DRAWN				SS			
4/8/05							
CHECKED							
APPROVED							
SIZE				PART NO.			
X				LHA-XX-TS			
REF:				SCALE: NTS			
				SHEET 1 OF 1			