





REV.	DATE	DESCRIPTION
A	01/13/99	UPDATE DRAWING
B	05/01/04	UPDATE DRAWING FORMAT
C	11/28/06	NOTE 2: CONTACT PIN TO SOLDER.



RECOMMENDED CABLE
STRIPPING DIMENSIONS



- NOTE:
1. CRIMPED FERRULE HEX CRIMP SIZE .128"
 2. CONTACT PIN TO SOLDER.

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	Amphenol Connex									
8						DRAWN	G.R.S.						11/28/06				
7						CHECKED											
6					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm	ISSUED			PART DESCRIPTION MCX CRIMP PLUG (FOR RG-174/U,188A/U,316/U)								
5	FERRULE	COPPER	GOLD	1		SHEET	1 OF 1										
4	CONTACT PIN	BRASS	GOLD	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”				PART NO. 252103								
3	INSULATOR	TEFLON	NATURAL	1		CAD FILE											
2	BODY	BER. COPPER	GOLD	1		C:/252/252103.DWG			DWG. NO.		252103.DWG	REV.	C	SIZE	A	SCALE	NA
1	HOUSING	BRASS	GOLD	1			DO NOT SCALE DRAWING										
	DESCRIPTION	MATERIAL	FINISH	QTY													