



Tip and Ring Common Mode Filters




These economical filters are designed to help telecommunications equipment engineers meet FCC and CCITT requirements. Available in 1 or 2 line (2 or 4 wire) versions, Coilcraft tip and ring filters provide >15 dB attenuation of common mode noise over the 3 Hz to 300 MHz frequency range.

Part number:	TRF 2000L (1-line) TRF 4000L (2-line)
Minimum inductance:	20 μ H
Rated current:	500 mA
DC resistance:	0.065 Ohms max
Dielectric strength¹:	1500 Vrms min

1. For TRF 2000, dielectric strength measured from pins 1,8 to 4,5. For TRF 4000, dielectric strength measured from pins 1,2,7,8 to pins 3,4,5,6.
2. Operating temperature range -40°C to $+85^{\circ}\text{C}$.
3. Electrical specifications at 25°C .

Typical Response*




*measured on HP 8753D network analyzer


TRF 2000



TRF 4000




TRF 2000L




Terminations: Tin-silver over tin


Recommended Board Layout



TRF 4000L



Recommended Board Layout



A max	B max	C max	D	E	F	G
0.425	0.550	0.475	0.115	0.300	0.100	0.300
10,80	13,97	12,07	2,92	7,62	2,54	7,62

Coilcraft[®]

Specifications subject to change without notice.
Please check our website for latest information.

Document 152 Revised 05/27/05