



Series 152FB

Fusion-Bonded Cable Jumpers

FEATURES

- Flexible Fusion-bonded Jumpers Plug Directly into PC Boards or Sockets
- Stranded Wire Conductors Fusion-bonded with an Overcoat of Sn for Easy Soldering or Socketing
- Jumpers Shipped with Protective Tabs on Ends to Maintaining Proper Conductor Spacing



GENERAL SPECIFICATIONS

- **INSULATION:** UL VW-1, Style 2651 Polyvinyl Chloride (PVC) with optional Polarization Stripe on one side
- **NOMINAL INSULATION THICKNESS:** 0.009 [0.23]
- **CONDUCTORS:** 26-gauge, 7-strand Cu with Sn fusion-bonded overcoat
- **OPERATING TEMPERATURE:** -4°F to 221°F [-20°C to 105°C]
- **VOLTAGE RATING:** 300Vrms
- **Dielectric Withstanding Voltage:** 1500Vrms
- **INSULATION RESISTANCE:** 10,000 MΩ per 10 feet [3.05 meters]
- **RESISTANCE:** 40.3Ω per 1000 feet [304.8 meters]
- **PROPAGATION DELAY:** 1.3ns/ft.


MOUNTING CONSIDERATIONS

- **SUGGESTED PCB HOLE SIZE:** 0.033 ± 0.002 [0.84 ± 0.05] dia.

ORDERING INFORMATION

| | | |
|---------------|---|--|
| XX-XXXX-152FB | X | Option |
| | | P = Polarization Strip, along one edge of cable* |
| | | Jumper Series |
| | | Cable Length "L" (inches) |
| | | 2.00" = 002 |
| | | 2.50" = 002.5 |
| | | 2.25" = 002.25 |
| | | 2.125" = 002.125 |
| | | Etc. |
| | | No. of Conductors |
| | | 4 thru 22 |

* Aries reserves the right to ship with or without unless specified by customer.



| # Conductors | Min. Insulation Length |
|--------------|------------------------|
| 4 thru 8 | 1.000 [25.40] |
| 9 and 10 | 1.250 [31.75] |
| 11 thru 22 | 1.500 [38.10] |

ALL DIMENSIONS: INCHES [MILLIMETERS]
 ALL TOLERANCES: ±0.005 [0.13] UNLESS OTHERWISE SPECIFIED
 ALL CABLES SHIP WITH Pb-FREE MATERIAL UNLESS CUSTOMER SPECIFIED WHEN ORDERING
 CONSULT FACTORY FOR OTHER SIZES AND CONFIGURATIONS

CUSTOMIZATION: ARIES SPECIALIZES IN CUSTOM DESIGN AND PRODUCTION. SPECIAL MATERIALS, PLATINGS, SIZES, AND CONFIGURATIONS CAN BE FURNISHED, DEPENDING ON QUANTITY.
 ARIES RESERVES THE RIGHT TO CHANGE PRODUCT GENERAL SPECIFICATIONS WITHOUT NOTICE
 PRINTOUTS OF THIS DOCUMENT MAY BE OUT-OF-DATE AND SHOULD BE CONSIDERED UNCONTROLLED