



Duo feed-through blocks with pluggable connection, type WKF

PC board connector

Spring clamp/rising cage clamp system



5 mm spacing

2.5 mm²



Rated voltages::
VDE 0110/01.89

250 V/4 kV/3 –
Overvoltage category III
400 V/4 kV/2 –
Overvoltage category II
1000 V/4 kV/1 –
Overvoltage category I



WKF 1,5 E/8113/35

fine-stranded solid V A
0.13 – 1.5 mm² 0.13 – 2.5 mm² 250 V/4 kV/3 16
No. 22-14
No. 24-14

5 mm



8 mm

WKF 1,5 E/35

fine-stranded solid V A
0.13 – 1.5 mm² 0.13 – 2.5 mm² 400 V/6 kV/3 17.5
No. 30-14 AWG 300 V 15 A
No. 30-14 AWG 600 V 15 A

5 mm



8 mm

Typ 8113 BFK

fine-stranded solid V A
0.13 – 2.5 mm² 0.13 – 4 mm² 12
No. 22-12 AWG 300 V 12 A

5 mm



9 mm

Type	Part No.	Std. Pack	Type	Part No.	Std. Pack	Std. Pack	G	T	Pole	Part No.
						5 mm spacing				
						unmarked				
						100	10,00	5,00	2	25.820.3253.0
						100	15,00	10,00	3	25.820.3353.0
WKF 1,5 E/8113/35	56.702.2053.0	100	WKF 1,5 E/35	56.702.7053.0	100	50	20,00	15,00	4	25.820.3453.0
						50	25,00	20,00	5	25.820.3553.0
						50	30,00	25,00	6	25.820.3653.0
35x27x7,5 EN 60715	98.300.0000.0	1	35x27x7,5 EN 60715	98.300.0000.0	1	50	35,00	30,00	7	25.820.3753.0
35x24x15 EN 60715	98.360.0000.0	1	35x24x15 EN 60715	98.360.0000.0	1	50	40,00	35,00	8	25.820.3853.0
9708/2 S35	Z5.522.8553.0	100	9708/2 S35	Z5.522.8553.0	100	50	45,00	40,00	9	25.820.3953.0
WEF 1/35	Z5.523.9353.0	100	WEF 1/35	Z5.523.9353.0	100	50	50,00	45,00	10	25.820.4053.0
APF 1,5/E/8113	07.312.4753.0	10	APF 1,5 E	07.312.3553.0	10	50	55,00	50,00	11	25.820.4153.0
						50	60,00	55,00	12	25.820.4253.0
						50	65,00	60,00	13	25.820.4353.0
						50	70,00	65,00	14	25.820.4453.0
IVB WKF 2,5 – 2	Z7.280.6227.0	10	IVB WKF 2,5 – 2	Z7.280.6227.0	10	50	75,00	70,00	15	25.820.4553.0
IVB WKF 2,5 – 3	Z7.280.6327.0	10	IVB WKF 2,5 – 3	Z7.280.6327.0	10	50	80,00	75,00	16	25.820.4653.0
IVB WKF 2,5 – 4	Z7.280.6427.0	10	IVB WKF 2,5 – 4	Z7.280.6427.0	10	marked				
IVB WKF 2,5 – 5	Z7.280.6527.0	10	IVB WKF 2,5 – 5	Z7.280.6527.0	10	100	10,00	5,00	2	25.820.0253.0
IVB WKF 2,5 – 6	Z7.280.6627.0	10	IVB WKF 2,5 – 6	Z7.280.6627.0	10	100	15,00	10,00	3	25.820.0353.0
IVB WKF 2,5 – 7	Z7.280.6727.0	20	IVB WKF 2,5 – 7	Z7.280.6727.0	20	50	20,00	15,00	4	25.820.0453.0
IVB WKF 2,5 – 8	Z7.280.6827.0	20	IVB WKF 2,5 – 8	Z7.280.6827.0	20	50	25,00	20,00	5	25.820.0553.0
IVB WKF 2,5 – 9	Z7.280.6927.0	20	IVB WKF 2,5 – 9	Z7.280.6927.0	20	50	30,00	25,00	6	25.820.0653.0
IVB WKF 2,5 – 10	Z7.280.7027.0	20	IVB WKF 2,5 – 10	Z7.280.7027.0	20	50	35,00	30,00	7	25.820.0753.0
LEL 1,5/1 WEISS	05.562.2453.0	100	LEL 1,5/1 WEISS	05.562.2453.0	100	50	40,00	35,00	8	25.820.0853.0
LEL 1,5/2 GRAU	05.562.2553.0	100	LEL 1,5/2 GRAU	05.562.2553.0	100	50	45,00	40,00	9	25.820.0953.0
LEL 1,5/3 SCHWARZ	05.562.2653.0	100	LEL 1,5/3 SCHWARZ	05.562.2653.0	100	50	50,00	45,00	10	25.820.1053.0
ADFN 2,5/4 GELB	04.343.8353.8	10	ADFN 2,5/4 GELB	04.343.8353.8	10	50	55,00	50,00	11	25.820.1153.0
AD 8113/4 GELB	04.343.6853.8	10	DIN 5264 B 0,6x3,5	06.502.4000.0	5	50	60,00	55,00	12	25.820.1253.0
DIN 5264 B 0,6x3,5	06.502.4000.0	5	DIN 5264 B 0,6x3,5 M	06.502.5000.0	10	50	65,00	60,00	13	25.820.1353.0
	05.561.0053.0	100				50	70,00	65,00	14	25.820.1453.0
						50	75,00	70,00	15	25.820.1553.0
						50	80,00	75,00	16	25.820.1653.0
						17- to 24- pole configurations upon request				
						Accessories: coding piece 05.561.9153.0				