




DESCRIPTION: ABOVE PCB, DECK AND PUSH ROD LOCATION ARE AS VIEW BY USER.

PRODUCT NO. 71299-XXXXX	PUSH-ROD LOCATION	STAND-OFF HEIGHT	① HEADER ASSY 71249-XXXX OR 61519-XXXX	② MECHANISM ASSY 72336-XXXXX	③ MATING RECEPTACLE	MOUNTING STYLE TO PCB AND PUSH-ROD SIDE
000CA	RIGHT	0.0	0000	72336-000CA	100 POSITION (2X50) 0.8mm RECEPTACLE PART NO. 73277-101000 PURCHASE SEPARATELY	 PCB
020CA	RIGHT	2.2	0022	72336-022CA		 PCB
040CA	RIGHT	4.3	0043	72336-043CA		 PCB
050CA	RIGHT	5.0	0050	72336-050CA		 PCB
050FA ②	RIGHT	5.0	0050	72336-050FA		
100CA	LEFT	0.0	0000	72336-100CA		
120CA	LEFT	2.2	0022	72336-122CA		
140CA	LEFT	4.3	0043	72336-143CA		
150CA	LEFT	5.0	0050	72336-150CA		
005CA	RIGHT	0.0	0500	72336-000CA		
025CA	RIGHT	0.0	0522	72336-000CA		
045CA	RIGHT	0.0	0543	72336-000CA		
055CA	RIGHT	0.0	0550	72336-000CA		
105CA	LEFT	0.0	0500	72336-100CA		
125CA	LEFT	0.0	0522	72336-100CA		
145CA	LEFT	0.0	0543	72336-100CA		
155CA	LEFT	0.0	0550	72336-100CA		

ORDERING INFORMATION

ORDER:






- EJECT HEADER ASSY (71299-XXXXX/XXXXLF)
- MATING RECEPTACLE (73277-101000/101402LF)

NOTE:

- SEE 71240 FOR DOUBLE-DECK APPLICATIONS.
- PUSH BUTTON LENGTH IS 21mm FOR 71299-050FA & 71299-050FALF(LEAD-FREE TYPE)

mat'l. code				surface ISO 1302			tolerance ISO 406 ISO 1101			projection ISO 1101			product family		
ltr ecn no dr date				tolerances unless otherwise specified			linear			angular			title		
L	V20120	RGD	1/18/02	.X±.3			MM			scale 1:1			CARDBUS SINGLE DECK		
M	V03-0552	WL	05/29/03	.XX±.13									ASSY SMT TYPE 123		
N	T04-0316	WL	07/12/04	±2"			.XXX±.051						dwg no		
P	N05-0034	WB	02/16/05	dr			R.GRAPE			7/3/96			sheet 1 of 1		
R	N08-0060	MZ	06/20/08	engr			D.BRANN			7/3/96			size		
S	ELX-N-011405	ZK	04/14/12	chr			D.BRANN			7/3/96			A4		
				appd			D.BRANN			7/3/96			type CUSTOMER		
sheet index				revision			sheet						Drawing		
				1			2			3					
				4			5			6					
				7			8			9					
				10			11								

DESCRIPTION: ABOVE PCB, DECK AND PUSH ROD LOCATION ARE AS VIEW BY USER.

PRODUCT NO. 71299-XXXX	PUSH-ROD LOCATION	STAND-OFF HEIGHT	① HEADER ASSY 71249-XXXX OR 61519-XXXX	② MECHANISM ASSY 72336-XXXX	③ MATING RECEPTACLE	MOUNTING STYLE TO PCB AND PUSH-ROD SIDE
000CALF	RIGHT	0.0	0000MLF	72336-000CA	100 POSITION (2X50) 0.8mm RECEPTACLE PART NO. 73277-101000 OR 73277-101402LF PURCHASE SEPARATELY	
020CALF	RIGHT	2.2	0022MLF	72336-022CA		
040CALF	RIGHT	4.3	0043MLF	72336-043CA		
050CALF	RIGHT	5.0	0050MLF	72336-050CA		
050FALF ②	RIGHT	5.0	0050MLF	72336-050FA		
100CALF	LEFT	0.0	0000MLF	72336-100CA		
120CALF	LEFT	2.2	0022MLF	72336-122CA		
140CALF	LEFT	4.3	0043MLF	72336-143CA		
150CALF	LEFT	5.0	0050MLF	72336-150CA		
151CALF	LEFT	5.0	0050MLF	72336-151CA		
005CALF	RIGHT	0.0	0500MLF	72336-000CA		
025CALF	RIGHT	0.0	0522MLF	72336-000CA		
045CALF	RIGHT	0.0	0543MLF	72336-000CA		
055CALF	RIGHT	0.0	0550MLF	72336-000CA		
105CALF	LEFT	0.0	0500MLF	72336-100CA		
125CALF	LEFT	0.0	0522MLF	72336-100CA		
145CALF	LEFT	0.0	0543MLF	72336-100CA		
155CALF	LEFT	0.0	0550MLF	72336-100CA		
156CALF	LEFT	0.0	0550MLF	72336-101CA		

ORDERING INFORMATION

ORDER:

- EJECT HEADER ASSY (71299-XXXX/XXXXLF)
- MATING RECEPTACLE (73277-101000/101402LF)

NOTE:

- SEE 71240 FOR DOUBLE-DECK APPLICATIONS.
- PUSH BUTTON LENGTH IS 21mm FOR 71299-050FA & 71299-050FALF(LEAD-FREE TYPE)



mat'l. code		surface ISO 1302		tolerance ISO 406 ISO 1181		projection ISO 1181		product family	
ltr ecn no dr date		tolerances unless otherwise specified		angles		linear .XX±.13 .XXX±.051		title	
S				±2°		scale 1:1		CARDBUS SINGLE DECK ASSY SMT TYPE 123	
dr		R.GRAPE 7/3/96		engr		D.BRANN 7/3/96		dwg no 71299	
chr		D.BRANN 7/3/96		appa		D.BRANN 7/3/96		sheet 2 of 11	
sheet index		revision sheet						A4	
								type CUSTOMER Drawing	

This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI.




Copyright FCI.

FCI CONFIDENTIAL

FCI



MATING RECEPTACLE
SHOWN FOR APPLICATION
CLARITY ONLY
MUST BE PURCHASED
SEPARATELY




mat'l. code				surface		tolerance		projection		product family					
				ISO 1302		ISO 406 ISO 1101									
ltr	ecn	no	dr	date	tolerances unless otherwise specified							title			
S					angles		.X±.3				CARDBUS SINGLE DECK ASSY SMT TYPE 123				
					linear	.XX±.13									
					±2'	.XXX±.051		scale:1:1							
					dr	R.GRAPE	7/3/96				dwg no		sheet4 of 1		size
					engr	D.BRANN	7/3/96				71299				A4
					chr	D.BRANN	7/3/96								
					appd	D.BRANN	7/3/96								
sheet	revision										type		CUSTOMER		Drawing
index	sheet														





FCI CONFIDENTIAL

This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI.
Copyright FCI.

PRODUCT NUMBER
71299-*****/****_LF






MATING RECEPTACLE
SHOWN FOR APPLICATION
CLARITY ONLY
MUST BE PURCHASED
SEPARATELY




P/N: 71299-640CA/640CALF
BELOW P.C.B.
LEFT PUSH-ROD
PCB LAYOUT 4 (SH.9)

mat'l. code				surface	tolerance	projection	product family
				ISO 1302	ISO 406 ISO 1101		
l	tr	ec	n	o	dr	date	title
S							CARDBUS SINGLE DECK ASSY SMT TYPE 123
				tolerances unless otherwise specified		MM	
				angles	.X±.3		
				line	.XX±.13		
				±2°	.XXX±.051	scale:1:1	
				dr	R.GRAPE	7/3/96	
				enr	D.BRANN	7/3/96	
				chr	D.BRANN	7/3/96	
				app	D.BRANN	7/3/96	
sheet	revision						
index	sheet						

PRODUCT NUMBER
71299-****/****LF



P/N: 71299-650CA
BELOW P.C.B.
LEFT PUSH-ROD
PCB LAYOUT 4 (SH.9)







P/N: 71299-050FA/-050FALF
(NOTE 2)

P/N: 71299-050CA/-050CALF
ABOVE P.C.B.
RIGHT PUSH-ROD
PCB LAYOUT 3 (SH.9)

mat'l. code		surface	tolerance	projection	product family
ISD 1302		ISD 406	ISD 118		
ltr ecn no dr date		tolerances unless otherwise specified			title
S		angles	.X±.3	linear	CARDBUS SINGLE DECK ASSY SMT TYPE 123
			.XX±.13	MM	
		±2"	.XXX±.051	scale 1:1	
		dr	R.GRAPE	7/3/96	dwg no 71299 sheet 6 of 1 size A4
		engr	D.BRANN	7/3/96	
		chr	D.BRANN	7/3/96	
		appd	D.BRANN	7/3/96	type CUSTOMER Drawing
sheet index	revision sheet				


PRODUCT NUMBER
71299-*****/****LF




mat'l. code	surface	tolerance	projection	product family
ISO 1302	ISO 406	ISO 1101	ISO 1101	
tolerances unless otherwise specified	angles	linear	MM	title
±.3	±.3	±.3	±.3	CARDBUS SINGLE DECK
±.13	±.13	±.13	±.13	ASSY SMT TYPE 123
±.051	±.051	±.051	±.051	dwg no
scale 1:1	scale 1:1	scale 1:1	scale 1:1	sheet 7 of 11
dr	R.GRAPE	7/3/96		size
enr	D.BRANN	7/3/96		A4
chr	D.BRANN	7/3/96		
appd	D.BRANN	7/3/96		
sheet index	revision	sheet		

FCI CONFIDENTIAL


P.C.B. LAYOUT FOR 2.2mm STANDOFF




SCALE 2:1



P.C.B.
LAYOUT 1
ABOVE PCB
AS ASSEMBLED



59.00±0.05



P.C.B.
LAYOUT 2
BELOW PCB
AS ASSEMBLED



This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI.

FCIconnect.com B

mat'l. code				surface		tolerance		projection		product family	
				ISO 1302		ISO 406 ISO 1101					
ltr ecn no dr date				tolerances		unless otherwise specified		title			
S				angles		.X±.3				CARDBUS SINGLE DECK	
				linear		.XX±.13				ASSY SMT TYPE 123	
				±2'		.XXX±.051		scale:1:1			
				dr		R.GRAPE		7/3/96		dwg no	
				engr		D.BRANN		7/3/96		sheet 8 of 1 size	
				chr		D.BRANN		7/3/96		A4	
				appd		D.BRANN		7/3/96		type CUSTOMER Drawing	
sheet index		revision sheet									

