


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS				DOC. NO.	SPC-F005	Effective:	12/21/98	DCP No.	860
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE	
170	A	RELEASED	SAS	07/09/99	JJC	6/27/00	DJC	7/11/00	

SPECIFICATIONS:

1. SAFETY SOCKET W/ Ø.080 [2.0] SOLDER HOLE
2. INSULATOR: POLYACETAL
3. CONTACT: BRASS, NICKEL PLATED
4. LOCKING NUT: BRASS, NICKEL PLATED
5. VOLTAGE: 1000V CATIII P2 (IEC1010-1)
6. CURRENT: 25A MAX.
7. RESISTANCE: <5 milliohms
8. TEMPERATURE: -20 °C TO +80 °C.
9. INSULATOR THREAD, M12 X 0.75 6.
10. MAXIMUM PANEL THICKNESS: .40 (10.2).



MOUNTING HOLE

ALL DIMENSIONS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES UNLESS OTHERWISE SPECIFIED				DRAWING TITLE:			
Fractions ± 1/32	Decimals .XX ± .01	XXX ± .005		SAFETY SOCKET, SOLDER FORK, RED			
DRAWN BY:	DATE:	SCOTT SERRITELLA	07/09/99	SIZE	DWG. NO.	ELECTRONIC FILE	REV
CHECKED BY:	DATE:	JOHN COLE	6/27/00	A	2271	92N4633.DWG	A
APPROVED BY:	DATE:	DANIEL CAREY	7/11/00	SCALE:	NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1

