

PRODUCT NUMBER

20020111-XXXXXXLF

20020111-□ □ □ □ A 0 □ LF

PITCH

C : 3.50 mm
D : 3.81 mm
G : 5.00 mm
H : 5.08 mm

POLES

02: 2 POLES
03: 3 POLES
04: 4 POLES

24: 24 POLES

LF : DENOTED ROHS COMPATIBLE

1 : STANDARD PRODUCT
W/ BOX PACKING

HOUSING CODE

CODE	COLOR	AVAILABILITY
1	GREEN(RAL 6018/T)	STANDARD
2	BLACK	ON REQUEST ONLY
3	GREY(RAL 7004/P)	ON REQUEST ONLY
4	BLUE(RAL 5015/A)	ON REQUEST ONLY

PROPERTY TABLE

FCI SERIES NAME		06-350	06-381	06-500	06-508
PITCH (mm)		3.50	3.81	5.00	5.08
VOLTAGE RATING (VAC)		300	300	300	300
CURRENT RATING (A)	cULus	10	10	12	12
	VDE	10.5	10.5	NA	NA
WITHSTANDING VOLTAGE (kV)	cULus	1.6	1.6	1.6	1.6
	VDE	2.5	2.5	NA	NA
OPERATING TEMP. (°C)		-40~+115	-40~+115	-40~+115	-40~+115
SOLDERING TEMP. (°C)		250±10 (5 sec.)	250±10 (5 sec.)	250±10 (5 sec.)	250±10 (5 sec.)
POLES AVAILABLE		02~24	02~24	02~24	02~24
SAFETY CERTIFICATE					

NOTES:

1. MATERIALS

1-1 HOUSING: THERMALPLASTIC RESIN, UL 94V-0 RATED.

1-2 TERMINAL: COPPER ALLOY, TIN PLATED.

2. PRODUCT SPECIFICATION REFER TO FCI GS-12-625.

3. BOXED PACKAGING,

DETAILED PRODUCT PACKING SPECIFICATION REFER TO FCI GS-14-1394.



4. FCI, SAFETY CERTIFICATE LOGO AND SERIES NAME TO BE SHOWN ON PRODUCT SURFACE.

5. THE PRODUCTS WHERE THE PART NUMBER END IN "LF" MEET THE EUROPEAN UNION DIRECTIVE AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.



6. RECOMENDED SOLDERING PROCESS BY WAVE SOLDER.

mat'l. code				surface ASME Y14.5		tolerance ASME Y14.5		projection		product family	
				ASME Y14.5		ASME Y14.5				TERMINAL BLOCK	
ltr ecn no dr date				tolerances unless otherwise specified				title			
A T10-0062 WL 050710				angles to face		X.±0.5[.020]		MM		TERMINAL BLOCK	
B T10-0155 WL 093010						X.X±0.3[.012]		[INCH]		PLUGGABLE, SOCKET, SIGNAL, R/A	
C T10-0187 WL 121410				X±1°		X.XX±0.1[.004]		scale		W/FLANGE	
D T11-0006 WL 012611				dr WENDY CHEN		042610				dwg no sheet 1 of 5 size	
E T11-0013 WL 040811				engr JASON HSU		042610				20020111 A.	
F T-004860 WL 080411				chr GARY HSIEH		042610					
				appd JOSEPH HSIA		042610					
sheet index		revision sheet		F 1	F 2	F 3	F 4	F 5		type CUSTOMER Drawing	


PRODUCT NUMBER	SERIES NAME	PITCH
20020111-DXXXXXXLF	06-381	3.81 mm



RECOMMENDED P.C.B LAYOUT



SECTION P-P



SECTION Q-Q




N= Number of poles

Dim A	$(N-1) \times 3.81 [.150] + 14.2 [.559]$
Dim B	$(N-1) \times 3.81 [.150]$
Dim C	$(N-1) \times 3.81 [.150] + 9.0 [.354]$
Dim D	$(N-1) \times 3.81 [.150]$



Poles	Tolerance
2p-6p	$\pm 0.15 [.006]$
7p-12p	$\pm 0.20 [.008]$
13p-16p	$\pm 0.25 [.010]$
17p-24p	$\pm 0.30 [.012]$

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection MM INCH	product family TERMINAL BLOCK
ltr	ecn	no	dr	date			title
F							TERMINAL BLOCK PLUGGABLE, SOCKET, SIGNAL, R/A W/FLANGE
				angles	$X \pm 0.5 [.020]$ $X.X \pm 0.3 [.012]$ $X.XX \pm 0.1 [.004]$	scale	dwg no
				dr	WENDY CHEN	042610	sheet 3 of 5
				enr	JASON HSU	042610	size
				chr	GARY HSIEH	042610	A4
				appd	JOSEPH HSIA	042610	type
sheet index	revision	sheet					CUSTOMER Drawing

PRODUCT NUMBER	SERIES NAME	PITCH
20020111-GXXXXXXLF	06-500	5.00 mm



RECOMMENDED PCB LAYOUT





N= NUMBER OF POLES

Dim A	$(N+2)*5.0[.197]$
Dim B	$(N-1)*5.0[.197]$
Dim C	$(N+1)*5.0[.197]$
Dim D	$(N-1)*5.0[.197]$



Poles	Tolerance
2P-6P	$\pm 0.15[.006]$
7P-12P	$\pm 0.20[.008]$
13P-18P	$\pm 0.25[.010]$
19P-24P	$\pm 0.30[.012]$

mat'l. code				surface ASME Y14.5 ✓		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK											
ltr ecn no dr date				tolerances unless otherwise specified								title									
F				 angle X'±1'		X.±0.5 [.020]		 MM [INCH] scale		TERMINAL BLOCK PLUGGABLE, SOCKET, SIGNAL, R/A W/FLANGE											
		X.X±0.3 [.012]																			
		X.XX±0.1 [.004]																			
		dr		WENDY CHEN		042610				dwg no					sheet 4 of 5		size				
		engr		JASON HSU		042610				20020111					A4						
		chr		GARY HSIEH		042610				type					CUSTOMER Drawing						
		appd		JOSEPH HSIA		042610															
sheet index		revision sheet																			


PRODUCT NUMBER	SERIES NAME	PITCH
20020111-HXXXXXXLF	06-508	5.08 mm



RECOMMENDED PCB LAYOUT



SECTION P-P



SECTION Q-Q

N= NUMBER OF CONCATS

Dim A	(N+2)*5.08[.200]
Dim B	(N-1)*5.08[.200]
Dim C	(N+1)*5.08[.200]
Dim D	(N-1)*5.08[.200]

Poles	Tolerance
2P-6P	±0.15[.006]
7P-12P	±0.20[.008]
13P-18P	±0.30[.012]
19P-24P	±0.40[.016]

mat'l. code	surface ASME Y14.5	tolerance ASME Y14.5	projection	product family
litr	ecn no	dr	date	TERMINAL BLOCK
F				title
				TERMINAL BLOCK
				PLUGGABLE, SOCKET, SIGNAL, R/A
				W/FLANGE
				dwg no
				sheet 5 of 5
				size
				A4
				type
				CUSTOMER Drawing
sheet index	revision	sheet		