


SMT MICRO HEADER & SOCKET

(1.27 mm) .050" PITCH • FTR/RSM SERIES






FTR
Mates:
RSM, SMS, SLM

RSM
Mates:
FTR, HTMS, HDWM,
DWM, TML, ZML, TMS

SPECIFICATIONS

Insulator Material:
Black Liquid Crystal Polymer
Contact Material:
RSM: Phosphor Bronze
Terminal Material:
FTR: Phosphor Bronze
Plating:
Au or Sn over
50 μ " (1.27 μ m) Ni
Operating Temp Range:
FTR: -55 °C to +105 °C with Tin;
FTR: -55 °C to +125 °C with Gold
RSM: -55 °C to +125 °C
Current Rating (FTR/RSM):
3.8 A per pin
(2 pins powered)
Voltage Rating:
290 VAC/410 VDC
Lead Size Accepted:
RSM: (0.46 mm) .018" SQ
Insertion Depth:
RSM: Top Entry =
(2.64 mm) .104" to (5.84 mm) .230"
with (0.38 mm) .015" wipe, or
pass-through.
RSM: Bottom Entry =
(5.49 mm) .216" minimum
(Add board thickness for
correct post OAL)





FTR	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	OPTION																						
		02 thru 40	Specify LEAD STYLE from chart	-F = Gold flash on contact, Matte Tin on tail -L = 10 μ" (0.25 μm) Gold on post, Matte Tin on tail -G = 10 μ" (0.25 μm) Gold on post, Gold flash on tail	-S = Single Row -D = Double Row	-XX" = Polarized -A = Alignment Pin (5 positions min. for -D) (Metal or plastic at Samtec discretion) (Not available with -LC) -LC = Locking Clip (6 positions min. for -D) (Not available with -A) (Manual placement required) -P = Plastic Pick & Place Pad (5 positions min. for -D) (8 positions min. for -S) -TR = Tape & Reel (4 positions min. for -S) -FR = Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks) (4 positions min. for -S)																						
					<table><thead><tr><th>LEAD STYLE</th><th>A</th></tr></thead><tbody><tr><td>-01</td><td>(5.84) .230</td></tr><tr><td>-02</td><td>(2.54) .100</td></tr><tr><td>-03</td><td>(3.18) .125</td></tr><tr><td>-51</td><td>(4.83) .190</td></tr><tr><td>-52</td><td>(5.21) .205</td></tr><tr><td>-53</td><td>(7.24) .285</td></tr><tr><td>-54</td><td>(8.51) .335</td></tr><tr><td>-55</td><td>(9.91) .390</td></tr><tr><td>-56</td><td>(10.29) .405</td></tr><tr><td>-57</td><td>(10.92) .430</td></tr></tbody></table>	LEAD STYLE	A	-01	(5.84) .230	-02	(2.54) .100	-03	(3.18) .125	-51	(4.83) .190	-52	(5.21) .205	-53	(7.24) .285	-54	(8.51) .335	-55	(9.91) .390	-56	(10.29) .405	-57	(10.92) .430	
LEAD STYLE	A																											
-01	(5.84) .230																											
-02	(2.54) .100																											
-03	(3.18) .125																											
-51	(4.83) .190																											
-52	(5.21) .205																											
-53	(7.24) .285																											
-54	(8.51) .335																											
-55	(9.91) .390																											
-56	(10.29) .405																											
-57	(10.92) .430																											
			-S	-D	-A	-LC																						



PROCESSING

Lead-Free Solderable:
Yes
SMT Lead Coplanarity:
RSM: (0.10 mm) .004" max
FTR: (0.10 mm) .004" max (02-20)
FTR: (0.15 mm) .006" max (21-40)*
*(.004" stencil solution may be available; contact ipg@samtec.com)

RSM	1	NO. PINS PER ROW	02	PLATING OPTION	ROW OPTION	OPTION
		02 thru 36		-F = Gold flash on contact, Matte Tin on tail -L = 10 μ " (0.25 μ m) Gold on contact, Matte Tin on tail	-S = Single Row -D = Double Row	-K = (6.25 mm) .246" DIA Polyimide film Pick & Place Pad (5 positions minimum for -D) (7 positions minimum for -S) -P = Plastic Pick & Place Pad (5 positions minimum for -D) (6 positions minimum for -S) -TR = Tape & Reel -FR = Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks)
						ALSO AVAILABLE Contact Samtec Other platings Locking clips



Note:
Some lengths, styles and options are non-standard, non-returnable.

samtec.com?FTR or samtec.com?RSM

F-224 (Rev 25APR25)

Unless otherwise approved in writing by Samtec, all parts and components are designed and built according to Samtec's specifications which are subject to change without notice.