



Visit Ohmite's Website at [www.ohmite.com](http://www.ohmite.com)**Stackohm Power Resistors**

- Small Size to Power Ratio
- All Welded Construction
- Low Profile and Stackable to Conserve Space
- Integral Mounting Bracket Conducts Heat to Mounting Surface

These oval shaped ceramic core resistors feature vitreous enamel coating and low profile to permit installation in spaces with minimal height. They are also equipped with integral mounting brackets so they can be fastened to a chassis and stacked in locations with limited surface area. When properly fastened, the mounting brackets add a heat sinking benefit resulting in smaller size per watt. The terminals are tinned lug with a hole. **Tolerance:** 5%.

Power Rating Watts	Fig.	Core Dimensions				A		B	
		Length (L)		Width (W)		Thk. (Th)		In.	mm
		In.	mm	In.	mm	In.	mm	In.	mm
10	1	.750	19.050	.375	9.525	.125	3.175	1.000	25.400
20	1	2.000	50.800	.375	9.525	.125	3.175	2.313	58.750
30	2	1.250	31.750	1.000	25.400	.250	6.350	2.000	50.800
40	2	2.000	50.800	1.000	25.400	.250	6.350	2.750	69.850
55	2	3.500	88.900	1.000	25.400	.250	6.350	4.250	107.950

Stock No.	Mfr.'s Type	Fig.	Ohms	Watts	EACH			
					1-9	10-24	25-49	50-99
290-2528	F10J1R0	1	1	10	4.98	4.82	4.60	4.27
290-2529	F10J5R0	1	5	10	4.98	4.82	4.60	4.27
290-2530	F10J10R	1	10	10	4.83	4.68	4.46	4.14
290-2534	F10J50R	1	50	10	4.83	4.68	4.46	4.14
290-2543	F10J2K5	1	2.5K	10	5.15	4.98	4.75	4.41
290-2556	F20J1R0	1	1	20	6.65	6.44	6.14	5.70
290-2557	F20J2R0	1	2	20	6.65	6.44	6.14	5.70
290-2559	F20J10R	1	10	20	6.05	5.85	5.58	5.19
290-2560	F20J15R	1	15	20	6.05	5.85	5.58	5.19
290-2561	F20J25R	1	25	20	6.05	5.85	5.58	5.19
290-2562	F20J100	1	100	20	5.63	5.45	5.20	4.83
290-2571	F20J250	1	250	20	5.63	5.45	5.20	4.83
290-2563	F20J300	1	300	20	5.63	5.45	5.20	4.83
290-2572	F20J500	1	500	20	5.63	5.45	5.20	4.83
290-2564	F20J1K0	1	1K	20	5.78	5.60	5.34	4.96
290-2573	F20J1K5	1	1.5K	20	5.78	5.60	5.34	4.96
290-2565	F20J2K0	1	2K	20	5.78	5.60	5.34	4.96
290-2567	F20J5K0	1	5K	20	5.78	5.60	5.34	4.96
290-2570	F20J15K	1	15K	20	6.15	5.95	5.68	5.27
290-2569	F30J50K	1	50K	20	9.15	8.85	8.45	7.84
290-2579	F30J1R0	2	1	30	8.53	8.26	8.00	7.76
290-2580	F30J2R0	2	2	30	8.53	8.26	8.00	7.76
290-2581	F30J3R0	2	3	30	8.53	8.26	8.00	7.76
290-2582	F30J5R0	2	5	30	8.53	8.26	8.00	7.76
290-2583	F30J15R	2	15	30	9.36	8.67	8.05	
290-2584	F30J25R	2	25	30	8.53	8.26	8.00	7.76
290-2585	F30J50R	2	50	30	8.53	8.26	8.00	7.76
290-2590	F30J75R	2	75	30	9.12	8.83	8.44	7.84
290-2591	F30J100	2	100	30	8.64	8.36	8.10	7.85
290-2594	F30J500	2	500	30	8.64	8.36	8.10	7.85
290-2596	F30J1K0	2	1K	30	8.64	8.36	8.10	7.85
290-2593	F30J3K0	2	3K	30	8.64	8.36	8.10	7.85
290-2600	F40J1R0	2	1	40	8.79	8.51	8.24	7.99

Stock No.	Mfr.'s Type	Fig.	Ohms	Watts	EACH				
					1-9	10-24	25-49	50-99	
290-2601	F40J1R5	2		1.5	40	8.79	8.51	8.24	7.99
290-2612	F40J2R0	2		2	40	8.79	8.51	8.24	7.99
290-2602	F40J3R0	2		3	40	8.79	8.51	8.24	7.99
290-2603	F40J4R0	2		4	40	8.79	8.51	8.24	7.99
290-2624	F40J5R0	2		5	40	8.79	8.51	8.24	7.99
290-2636	F40J10R	2		10	40	8.57	8.29	7.91	7.34
290-2648	F40J25R	2		25	40	9.42	9.11	8.70	8.08
290-2649	F40J50R	2		50	40	8.74	8.46	8.19	7.94
290-2672	F40J100	2		100	40	8.74	8.46	8.19	7.94
290-2687	F40J250	2		250	40	8.74	8.46	8.19	7.94
290-2698	F40J500	2		500	40	8.74	8.46	8.19	7.94
290-2608	F40J1K0	2		1K	40	8.74	8.46	8.19	7.94
290-2645	F40J2K0	2		2K	40	8.74	8.46	8.19	7.94
290-2609	F40J2K5	2		2.5K	40	8.74	8.46	8.19	7.94
290-2609	F40J10K	2		10K	40	8.09	8.70	8.43	8.19
290-2632	F40J15K	2		15K	40	9.53	9.22	8.80	8.17
290-2644	F								