




- 1 NYLON, UL 94V-0 RATED, RED.
- 2 BRASS PER ASTM B36.
- 3 3.81µm [0.000150] MIN TIN OVER 2.54µm [0.000100] MIN COPPER.
- 4 0.76µm [0.000030] MIN GOLD FOR A LENGTH OF 5.08 [0.200] FROM MATING END, 3.81µm [0.000150] MIN TIN FOR A LENGTH OF 4.83 [0.190] MIN FROM OPPOSITE END, BOTH OVER 1.27µm [0.000050] MIN NICKEL.
- 5 CONTACTS SELECT LOADED IN POSITIONS 2, 3 AND 4.
- 6 3.81µm [0.000150] MIN TIN OVER 2.54µm [0.000100] MIN COPPER.
- 7 0.76µm [0.000030] MIN GOLD FOR A LENGTH OF 5.08 [0.200] FROM MATING END, 3.81µm [0.000150] MIN TIN FOR A LENGTH OF 4.83 [0.190] MIN FROM OPPOSITE END, BOTH OVER 1.27µm [0.000050] MIN NICKEL.
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	T	REVISED PER ECO-16-004940	29JUL2016	NK	MZ
	U	REVISED PER ECO-18-000437	18JAN2018	RS	MZ

RECOMMENDED PC BOARD LAYOUT

8 5	OBSOLETE	6	YES	1-207119-2
	OBSOLETE	7	NO	1-207119-1
		7	YES	1-207119-0
		6	NO	207119-9
		6	YES	207119-8
8 5	OBSOLETE	3	YES	207119-7
	OBSOLETE	4	NO	207119-4
	OBSOLETE	4	YES	207119-3
	OBSOLETE	3	NO	207119-2
	OBSOLETE	3	YES	207119-1
		CONTACT FINISH	MOUNTING TABS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	03/10/92		 TE Connectivity								
		CHK	3-17-92										
DIMENSIONS: mm [INCHES]		L.SIPE		NAME PIN HEADER ASSEMBLY, 4 POSITION, METRIMATE									
		R.STONE											
		APVD	—										
		PRODUCT SPEC											
		108—10033											
		APPLICATION SPEC											
MATERIAL		—		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO						
		WEIGHT		A2	00779	C=207119	—						
HOUSING: 1		CONTACT: SEE TABLE				CUSTOMER DRAWING		SCALE	4:1	SHEET	1 of 1	REV	U