








LOC	DIST	REVISIONS			
		LTR	DESCRIPTION	DATE	APVD
H	-	A	EH10-0183-05	10 FEB 05	JvdH
		-	-	-	-
		-	-	-	-




NOTE:
1 TOLERANCE UNLESS OTHERWISE SPECIFIED: $\pm 0,15\text{mm}$.



1,27 TYP.
3,81



7,62



PRINTED CIRCUIT BOARD LAYOUT

(VIEW SHOWN IS CIRCUIT (NONCOMPONENT) SIDE OF BOARD.)
PRINTED CIRCUIT BOARD THICKNESS: 1,6 mm NOMINAL.
TOLERANCE UNLESS OTHERWISE SPECIFIED: $\pm 0,05$.

IN CONTACT AREA: 0,15µm SEL. GOLDFLASH. OVER 1,2µm MIN. NICKEL. CONTACT INSERT: SOLDER TINES: 2,5µm MIN. TIN OVER 1,2µm MIN. NICKEL.	HOUSING, COLOR BLACK: PBT 20% GF, UL 94V-0 CONTACT INSERT: PBT, UL 94V-0 CONTACTS: PH, BRONZE	290 PCS IN A TRAY	1-1705949-1
		TAPE MOUNTED 1000pcs./reel	1705949-1
FINISH	MATERIAL	PACKAGING	PARTNUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR Tyco Electronics Nederland B.V. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN J.V.D.HEIJDEN.	AMP Tyco Electronics Nederland B.V. s-HERTOGENBOSCH, THE NETHERLANDS				
		CHK P.WILLEMS.					
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J.BROEKSTEEG.	NAME				
	0 PLC ± -	PRODUCT SPEC -	MODULAR JACK SIDE ENTRY 4/4 FOR PRINTED CIRCUIT BOARD.				
	1 PLC ± -						
	2 PLC ± -						
	3 PLC ± -						
	4 PLC ± -						
ANGLES ± 0.2°		APPLICATION SPEC 114-19019	SIZE	CAGE CODE	DRAWING NO		
MATERIAL	FINISH	WEIGHT -	A2	00779	C= 1705949		
					SCALE 4:1	SHEET 1 OF 1	REV A