



Standard



Adjusting program (CAL):
For quick setting of the balance's accuracy. External adjusting weight required.



Weighing units: can be switched to e.g. non-metric units at the touch of a key. See balance model.



Spray and dust protection: The type of protection is shown by the pictogram. For a definition see the glossary, page 96.



Stainless steel: the balance is protected against corrosion.



Animal weighing program: strong vibrations are filtered out.



Battery operation:
The battery type is specified for each device.



Tare: put back displayed value to „0“ during weighing process, e.g. to add or remove weighing material from a container.

Order Hotline:
Go to back page of catalogue



KERN HCB

Both models:

Snap link

included, stainless steel with safety catch, aperture 15 mm. Can be reordered, KERN HCB-A01

Multi data hold function

✓ By pressing the Hold key the

- weight display can be "frozen" for 5 sec
- weight display can be "frozen" until any key is pressed
- ✓ when the weighing value remains unchanged
- the weight display is automatically "frozen" for 5 sec
- the weight display is automatically "frozen" until any key is pressed

LCD display

digit height 12 mm

Peak load display (Peak Hold)

displays the highest load value (peak load) of a weighing, measuring frequency 5 Hz



Ready for use












Batteries included.
HCB: Size AA (2 x 1.5 V), Operating time approx. 300h.
HCN: Size AA (2 x 1.5 V), Operating time approx. 200h.
AUTO-OFF function after 3 min without a change of load to preserve the batteries, can be switched off

S-hook stainless steel, included. Aperture approx. 25 mm. Can be reordered, HCB-A02



KERN HCN

STANDARD



Model	Weighing range	Read-out	OPTION
	Max	d	Certifi- cate KERN
KERN	kg	g	
HCB 20K10	20	10	963-128
HCB 20K50	20	50	963-128
HCB 50K20	50	20	963-128
HCB 50K100	50	100	963-128
HCB 99K50	99	50	963-129
HCB 100K200	100	200	963-129
HCB 200K100	200	100	963-129
HCB 200K500	200	500	963-129
stainless steel			
HCN 20K50IP	20	50	963-128
HCN 50K100IP	50	100	963-128
HCN 100K200IP	100	200	963-129
HCN 200K500IP	200	500	963-129

KERN HCB Housing, plastic WxDxH 80x45x150 mm. Total height with snap link and S-hook 290 mm. Net weight approx. 400 g.

KERN HCN Housing, stainless steel WxDxH 95x55x175 mm. Total height with snap link and S-hook 315 mm. Net weight approx. 1.5 kg.



KERN - Your DKD-Calibration Partner

issues DKD calibration certificates for balances and test weights in its own accredited laboratories. It is internationally valid.

KERN is a manufacturer of test weights in the international classes of accuracy

E1, E2, F1, F2, M1, M2, M3, from 1 mg up to 2000 kg

DKD = German
Calibration
Service



Your KERN specialist dealer