

SPRING-LOADED CONNECTORS

SERIES 319, 399 • .100" GRID TARGET CONNECTORS FOR SPRING-LOADED ASSEMBLIES • SINGLE ROW STRIPS






FIG. 1



Coplanarity .005". For Pin counts >10 positions, consult Technical Support.

FIG. 2



Coplanarity .005". For Pin counts >10 positions, consult Technical Support.

FIG. 3





FIG. 4

- Series 319 and 399 Spring Target Connectors, supplied in single row strips. Available in SMT and right angle through-hole termination configurations
- Target Connectors provide an excellent gold-plated conductive mating surface for spring loaded connectors. These series are offered with a flat face for making contact with our standard .042" dia. spring pin plungers
- Target connectors use MM #1940, #1941/1942, #1953 and #1954 pins. See pages 218 & 223.3 for details
- Insulators are high temperature thermoplastic



ORDERING INFORMATION

FIG. 1	Series 319...041	Surface Mount w/ Alignments Pins
	319-10-1	-30-041000 Specify number of pins 03-64
FIG. 2	Series 319...008	Surface Mount
	319-10-1	-30-008000 Specify number of pins 01-64
FIG. 3	Series 319...054	Low Profile Surface Mount
	319-10-1	-30-054000 Specify number of pins 01-64
FIG. 4	Series 399...008	Right Angle Solder Tails
	399-10-1	-10-008000 Specify number of pins 01-64
RoHS-2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Environmental Data, See page 264		
SPECIFY PLATING CODE XX=		
Pin Plating 		
	10 	
	10 μ" Au	

