



290CX



DIMENSIONS:

A	3.125" $\pm$ 0.063
B	4.063" $\pm$ 0.125
C	3.750" $\pm$ 0.063
D	1.975" $\pm$ 0.063
E	2.500" $\pm$ 0.063
F	3.125" $\pm$ 0.063

NOTE: ALL LEADS 9" OUT MIN., STRIPPED .5"



ELECTRICAL DATA:

Turns ratio:	1 : 5.96 (RED - RED)
Exciting Current	@ 120V, 60Hz, BLK - BLK = 258mA Max.
DCR	@ 20C, BLK - BLK = 1.539 Ω $\pm$ 20%
	@ 20C, RED - RED = 83.99 Ω $\pm$ 20%
	@ 20C, YEL - YEL = 0.041 Ω $\pm$ 20%
	@ 20C, GRN - GRN = 0.054 Ω $\pm$ 20%
Pri. Voltage	120V 60Hz
Sec. Voltage (RMS)	650VCT @ 207mA C/W 50V TAP, 5V @ 3A / 6.3VCT @ 4A
No Load Voltage	715.18VCT/ 5.30V / 6.75V

HAMMOND
ELECTRONICS

52 RANKIN PLACE,
WATERLOO, ONTARIO, N2L 3Z5.

PHONE (519) 886-6181
FAX # (519) 886-9540

TITLE

290CX

2	08/11/09	Updated Electrical Data	I.P.	DR BY IOAN POP
1	05/12/09	PRELIMINARY	I.P.	DATE 07/04/08
NO	DATE	REVISION		DIM IN(X)MM()

290CX