

10 9 8 7 6 5 4 3 2 1

F

E

D

C

B

A

F






E

D


C

B

A



SECTION A-A



SECTION B-B

- NOTE
1. MATERIAL : COPPER ALLOY (t=0.15)
 2. FINISH : REFLOWED PRE-PLATED TIN PLATING ON OVERALL THICKNESS 0.4μm Min, UNDER PLATING CU OVERALL THICKNESS 0.1 μm Min
 3. APPLICABLE HOUSING : 104092,104105, 104121 SERIES
 4. PACKAGING SPECIFICATION : PK-104521-001
 5. CRIMPING SPECIFICATION : CS-104521-001
 6. APPLICABLE CABLE WIRE RANGE : #26~#32'
 7. PLEASE DON'T DAMAGE, DENT AND DON'T MAKE IT DIRTY. BECAUSE THE RANGE IN THE SHADED PORTION SHOWN IN FIGURE IS THE CONTACT AREA.

ORDER NO. 104521-6001

RELEASED EC NO: KOR2011-0072 DRWN:HTSUNG 2011/01/10 CHKD:SHCHU 2011/01/10 APPR:YUNSIKKIM 2011/01/10 A	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ◻=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 20:1		DESIGN UNITS METRIC		THIRD ANGLE PROJECTION 		
				mm	INCH	DRAWN BY HTSUNG	DATE 2010/08/09	TITLE 1.25 W/B CONN. PLUG TERMINAL					
			4 PLACES	± ---	± ---	CHECKED BY SHCHU	DATE 2010/08/09						
			3 PLACES	± ---	± ---	APPROVED BY YSKIM		DATE 2010/08/09		molex MOLEX INCORPORATED			
			2 PLACES	± 0.25	± ---								
			1 PLACE	± 0.3	± ---	MATERIAL NO. 1045216001		DOCUMENT NO. SD-104521-001		SHEET NO. 1 OF 1			
			ANGULAR ± 1 °										
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A3 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										

9 8 7 6 5 4 3 2 1