

Power Rheostats


100 Watt



FEATURES


- Diameter 3 5/32" [80.17mm]
- Depth behind panel 1 1/2" [38.10mm]
- Shaft 1/4" [6.35mm] diameter
- Rotation 300° ± 5°
- Weight 0.594 pounds (268 grams)
- Mounts on panels up to 1/4" [6.35mm] by means of a 3/8" [9.52mm], 32 bushing and hex nut
- Non-turn lugs require 3/16" [4.76mm] hole, 1/2" [12.70mm] below center of shaft - Model "A" shaft
- U. L. Listed, File No. E51076

DIMENSIONS in inches [millimeters]



DERATING





Angstromhm rheostat standard wattage ratings are based on a 300°C rise in "free-air" in ambient not exceeding + 40°C (shown). For other applications, wattage ratings are available based on 340°C rise in "free-air" in ambient not exceeding + 25°C, and in other cases + 50°C.



RESISTANCE VALUES*		
TOTAL OHMS	MAXIMUM AMPS	APPROXIMATE STEPS
0.5	14.140	30
1.0	10.000	30
2.0	7.071	56
3.0	5.774	66
5.0	4.472	56
7.5	3.652	66
10.0	3.162	104
15.0	2.582	113
25.0	2.000	144
50.0	1.414	180
75.0	1.155	180
100.0	1.000	216
200.0	0.707	252
300.0	0.557	252
400.0	0.500	252
500.0	0.447	324
750.0	0.365	396
1000.0	0.316	410
2000.0	0.224	410
2500.0	0.200	410
5000.0	0.141	685
7500.0	0.115	820
10000.0	0.100	820

* All other intermediate resistance values are available and can be manufactured on a normal delivery cycle.

SPECIAL SHAFTS in inches [millimeters]

 <p>TYPE B: 1/2 [12.70], 11/32 [8.73] Models. Slotted shaft with standard bushing for 1/8 [3.18] panel.</p>	 <p>TYPE C: 3/4 [19.05], 5/8 [15.88] Models. Locking bushing with slotted shaft for 1/4 [6.35] panel.</p>	 <p>TYPE D: 5/8 [15.88], 1/2 [12.70] Models. Locking bushing with slotted shaft for 1/8 [3.18] panel.</p>	 <p>TYPE E: 27/32 [21.43], 11/32 [8.73] Models. Std. bushing and flattened shaft w/screwdriver slot for 1/8 [3.18] panel.</p>
---	---	--	---

MARKING

- Resistance value
- Amps
- Date code

ORDERING INFORMATION

MP25 MODEL A BUSHING AND SHAFT CONFIGURATION 25 VALUE

A = Standard Flatted Shaft

NOTE: For Additional Features: Submit detailed drawing information when ordering "non-standard" parts.



Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.