


GP Batteries


Data Sheet

Model No.: GP70AAAH


Type	Rechargeable Nickel Metal Hydride Cylindrical Cell		
Nominal Dimension (with Sleeve)	$\Phi = 10.5\text{mm}$ $H = 43.7\text{mm}$		
Applications	Recommended discharge current 70 to 2100mA		
Nominal Voltage	1.2V		
Capacity	Minimum: 700mAh Typical: 730mAh when discharged at 140mA to 1.0V at 20°C		
Charging Condition	70mA for 16 hrs at 20°C		
Fast Charge	350mA to 700mA (0.5 to 1C) charge termination control recommended control parameters: - ΔV : 0 - 5mV DT/dt : 0.8°C/min (0.5 to 0.9C) : 0.8 - 1°C/min (1C) TCO : 45 - 50°C Timer : 105% nominal input		
Service Life	>500 cycles (IEC standard)		
Continuous Overcharge	70mA maximum current for 1 year No conspicuous deformation and/or leakage		
Weight	13.0g		
Internal Resistance	Average 35m Ω upon fully charged (Range 20-40m Ω) at 1000Hz		
Max. Charging Voltage	1.5V at 70mA charging		
Ambient Temperature Range	Standard Charging	:	0 to 45°C
	Fast Charging	:	10 to 45°C
	Discharging	:	-20 to 50°C
	Storage	:	-20 to 35°C




Fast Charge (Charge control required)



Low Rate Discharge



High Rate Discharge



* The information (subject to change without prior notice) contained in this document is for reference only and should not be used as a basis for product guarantee or warranty. For applications other than those described here, please consult your nearest GP Sales and Marketing Office or Distributors.



Member
Gold Peak Group

Manufacturer reserves the right to alter or amend the design, model and specification without prior notice.

CRS3504 Rev.03