

5

4

3

2

1

受控 CONTROLLED DOCUMENT

编号 P/N	40-9415HDM-CUST	版本 Rev	02	日期 Rel'd Date	Aug9,11
-----------	-----------------	-----------	----	------------------	---------



Description: HI-Density Crimp 15 Pin Male

Part No: 40-9415HDM

Application: 94 Series D-Sub Connector

Crimp Tool: N/A

Impedance: N/A

Frequency Range: N/A

Material: Shell Steel, Tin plated

Insulator PBT+Fiber-grass, UL94-V0

RoHS Compliance: Yes

Technical Detail: N/A

DRAWING NO.

40-9415HDM-CUST

REVISIONS

01

OFFICIAL RELEASE

11-26-09

Y

U

Y

U

T

H

02

CHANGE DIMENSION

FROM 9.3 TO 7.0

07-01-11

L

H

M

M

M

M

M

M

M

M

M

M

M

M


M

M

M

ECO-11-0127

CUSTOMER COPY



TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY Wencan Li	DATE 07-01-11
DECIMALS	mm	CHECKED BY Hu Yuge	DATE 07-01-11
X	± 0.5	APPROVED BY Ma Lin	DATE 07-01-11
X.X	± 0.3		
X.XX	± 0.2		
ANGLES	± 0.5°	U/M	mm

THIS DRAWING WAS PRODUCED BY COMPUTER,
DO NOT SCALE DRAWING OR UPDATE MANUALLY.

 EMERSON. Network Power		Connectivity Solutions	
TITLE HI-DENSITY CRIMP 15 PIN MALE			
SHEET 1 OF 1	DRAWING NO. 40-9415HDM-CUST		SIZE A

5

4

3

2

1