

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
	-		G6	ECR-15-012364	20AUG2015	SS	RR

2pol.
8-927 742-2

2pol.
0-927 742-2
5-927 742-5
9-927 742-2

3pol.
0-927 742-3
1-927 742-3
5-927 742-3
9-927 742-3


4pol.
0-927 742-4
9-927 742-4

5pol.
0-927 742-5

6pol.
0-927 742-6
5-927 742-6
6-927 742-6
7-927 742-6
8-927 742-6

7pol.
0-927 742-7
2-927 742-7

8pol.
0-927 742-8



SCALE 1:1

1 TYPICAL CAVITY SUITABLE FOR:
FASTIN-FASTON TAB CONTACTS 6.3 mm SRS:
P/N: 60294, 0.3-0.8 mm2 WIRE RANGE
160691, 0.3-0.8 mm2 WIRE RANGE
AMPLIVAR CONTACTS:
P/N: 141051, 0.1-0.5 mm2 WIRE RANGE
142411, 0.3-1.6 mm2 WIRE RANGE
MAX. INSULATION DIA. 2.8 mm,
MAX. INSULATION CRIMP WIDTH 3.3 mm.

2) SEE TABLE FOR SUITABLE COUNTERPART.

3 CIRCUIT IDENTIFICATION No. ACCORDING TO DIN 1451.

4 POLARIZATION KEYS DIMENSIONS AND POSITIONS
ARE ACCORDING TO "RAST 5" NORM

5 TE TRADEMARK "LOGO" AND
TYCO ELECTRONICS "PART NUMBER"
OPTIONAL POSITION.




6) PACKAGING ACCORDING TO TE SPEC. 107-20248.

7 PRODUCT ACCORDING TO IEC 60335-1 NORM.


8 NOT TOOLED YET.

9 SPECIAL VERSION WITH LARGER GAP "A"

10 PRELIMINARY - NOT YET RELEASED FOR PRODUCTION




PANEL CUT DIMENSIONS
SCALE 1:1



12	-	-	-	-	-	-	-	-	-	-	-
11	-	-	-	-	-	-	-	-	-	-	-
10	-	-	-	-	-	-	-	-	-	-	-
9	-	-	-	-	-	-	-	-	-	-	-
8	-	-	-	-	-	-	-	-	-	-	-
7	44	30	35	2-927 742-7	0-927 740-7	3-828 353-7	UL94V-2	black	-		
7	44	30	35	0-927 742-7	0-927 740-7	3-828 353-7	UL94V-2	natur	-		
6	39	25	30	8-927 742-6	0-927 740-6	-	UL94-V0	natur	-	7	
6	39	25	30	7-927 742-6	0-927 740-6	-	UL94V-2	natur	-	7	
6	39	25	30	6-927 742-6	0-927 740-6	-	UL94V-0	black	-		
6	39	25	30	5-927 742-6	0-927 740-6	-	UL94V-0	natur	-		
6	39	25	30	0-927 742-6	0-927 740-6	-	UL94V-2	natur	-		
5	34	20	25	0-927 742-5	0-927 740-5	3-828 353-6	UL94V-2	natur	-	9	
4	29	15	20	9-927 742-4	0-927 740-4	3-828 353-4	UL94V-2	natur	-	7	
4	29	15	20	0-927 742-4	0-927 740-4	3-828 353-4	UL94V-2	natur	-		
3	24	10	15	9-927 742-3	0-927 740-3	4-828 353-3 6-828 353-3	UL94V-2	natur	-	7	
3	24	10	15	5-927 742-3	0-927 740-3	4-828 353-3 6-828 353-3	UL94V-0	natur	-		
3	24	10	15	2-927 742-3	0-927 740-3	4-828 353-3 6-828 353-3	UL94V-2	grey	-		
3	24	10	15	1-927742-3	927740-3	4-828353-3 6-828353-3	UL94V-2	natur	l	7	9
3	24	10	15	0-927 742-3	0-927 740-3	4-828 353-3 6-828 353-3	UL94V-2	natur	-		
2	19	5	10	9-927 742-2	4-927 740-2	-	UL94V-2	natur	-	7	
2	19	5	10	8-927 742-2	-	-	UL94V-2	natur	-	7	
2	19	5	10	5-927 742-2	4-927 740-2	-	UL94V-0	natur	-		
2	19	5	10	0-927 742-2	4-927 740-2	-	UL94V-2	natur	-	9	
POS.	W	X	Y	PART-NO.	STANDARD TIMER	MULTI-FIT	MATERIAL	COLOUR	REV.	NOTE	

PARTS LIST

THIS DRAWING IS UNPUBLISHED. IT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE USER SHALL BE RESPONSIBLE FOR THE LATEST VERSION. SHOULD BE CONTACTED FOR THE LATEST VERSION.				DWN CHK G. TURCO	Z2MAR2005	Tyco Electronics AMP Italia S.p.A. Corso F.lli Cervi, 15 COLLENO (TO)			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	2-12 POS. FASTIN-FASTON CONNECTOR TAB HOUSING RAST 5, PANEL MOUNT VERSION				
		1 P/LC ±0.1 1 P/LC ±0.2 2 P/LC ±0.2 3 P/LC ±0.1 4 P/LC ±0.1 ANGLES ±1°		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -	SIZE A1	CAGE CODE 00779	DRAWING NO C=927742	RESTRICTED TO -	
MATERIAL SEE TABLE		FINISH SEE TABLE		CUSTOMER DRAWING		SCALE 5:1	SHEET 1	OF 1	REV G6